



SIRIUS SOFT STARTER, SIZE S00, 9A, 4KW/400V, 40 DEGREES, 200-480V AC, 110-230V AC/DC, SPRING-LOADED TERMINALS

General technical data:

| | | |
|---|--|--------|
| product brand name | | SIRIUS |
| Product feature | | |
| <ul style="list-style-type: none"> • integrated bypass contact system | | Yes |
| <ul style="list-style-type: none"> • Thyristors | | Yes |
| Product function | | |
| <ul style="list-style-type: none"> • Intrinsic device protection | | No |
| <ul style="list-style-type: none"> • motor overload protection | | No |
| <ul style="list-style-type: none"> • Evaluation of thermistor motor protection | | No |
| <ul style="list-style-type: none"> • External reset | | No |
| <ul style="list-style-type: none"> • Adjustable current limitation | | No |
| <ul style="list-style-type: none"> • inside-delta circuit | | No |
| Product component Motor brake output | | No |
| Equipment marking acc. to DIN EN 61346-2 | | Q |
| Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750 | | G |

Power Electronics:

| | | |
|--|---|---|
| Product designation | | soft starters for standard applications |
| Operating current | | |
| <ul style="list-style-type: none"> • at 40 °C Rated value | A | 9 |
| <ul style="list-style-type: none"> • at 50 °C Rated value | A | 8 |
| <ul style="list-style-type: none"> • at 60 °C Rated value | A | 7 |
| Mechanical power output for three-phase motors | | |
| <ul style="list-style-type: none"> • at 230 V | | |

| | | |
|---|--------------|-------------|
| — at standard circuit at 40 °C Rated value | W | 2 200 |
| • at 400 V | | |
| — at standard circuit at 40 °C Rated value | W | 4 000 |
| yielded mechanical performance [hp] for three-phase AC motor at 200/208 V at standard circuit at 50 °C Rated value | metric hp | 2 |
| Operating frequency Rated value | Hz | 50 ... 60 |
| Relative negative tolerance of the operating frequency | % | -10 |
| Relative positive tolerance of the operating frequency | % | 10 |
| Operating voltage at standard circuit Rated value | V | 200 ... 480 |
| Relative negative tolerance of the operating voltage at standard circuit | % | -15 |
| Relative positive tolerance of the operating voltage at standard circuit | % | 10 |
| Minimum load in % of I _M | % | 10 |
| Continuous operating current in % of I _e at 40 °C | % | 115 |
| Active power loss at operating current at 40 °C during operation typical | W | 1 |

Control electronics:

| | | |
|---|----|-------------|
| Type of voltage of the control supply voltage | | AC/DC |
| Control supply voltage frequency 1 Rated value | Hz | 50 |
| Control supply voltage frequency 2 Rated value | Hz | 60 |
| Relative negative tolerance of the control supply voltage frequency | % | -10 |
| Relative positive tolerance of the control supply voltage frequency | % | 10 |
| Control supply voltage 1 with AC at 50 Hz | V | 110 ... 230 |
| Control supply voltage 1 with AC at 60 Hz | V | 110 ... 230 |
| Relative negative tolerance of the control supply voltage with AC at 60 Hz | % | -20 |
| Relative positive tolerance of the control supply voltage with AC at 60 Hz | % | 20 |
| Control supply voltage 1 for DC | V | 110 ... 230 |
| Relative negative tolerance of the control supply voltage for DC | % | -20 |
| Relative positive tolerance of the control supply voltage for DC | % | 20 |
| Display version for fault signal | | red |

Mechanical data:

| | | |
|-------------------------------|----|-----|
| Size of engine control device | | S00 |
| Width | mm | 45 |
| Height | mm | 120 |
| Depth | mm | 150 |

| | | |
|--|----|--|
| Mounting type | | screw and snap-on mounting |
| mounting position | | With vertical mounting surface +/-10° rotatable, with vertical mounting surface +/- 10° tiltable to the front and back |
| Required spacing with side-by-side mounting | | |
| • upwards | mm | 60 |
| • at the side | mm | 15 |
| • downwards | mm | 40 |
| Installation altitude at height above sea level | m | 5 000 |
| Cable length maximum | m | 300 |
| Number of poles for main current circuit | | 3 |

Connections/ Terminals:

| | | |
|---|--|--|
| Type of electrical connection | | |
| • for main current circuit | | spring-loaded terminals |
| • for auxiliary and control current circuit | | spring-loaded terminals |
| Number of NC contacts for auxiliary contacts | | 0 |
| Number of NO contacts for auxiliary contacts | | 1 |
| Number of CO contacts for auxiliary contacts | | 0 |
| Type of connectable conductor cross-section for main contacts for box terminal using the front clamping point | | |
| • solid | | 2x (1 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²) |
| • finely stranded with core end processing | | 2x (1.5 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²) |
| Type of connectable conductor cross-section for AWG conductors for main contacts for box terminal | | |
| • using the front clamping point | | 2x (16 ... 10) |
| Type of connectable conductor cross-section for main contacts | | |
| • solid | | 1 ... 4 mm ² |
| • finely stranded with core end processing | | 1 ... 2.5 mm ² |
| Type of connectable conductor cross-section for auxiliary contacts | | |
| • solid | | 2x (0.25 ... 2.5 mm ²) |
| • finely stranded with core end processing | | 2x (0.25 ... 1.5 mm ²) |
| Type of connectable conductor cross-section for AWG conductors | | |
| • for main contacts | | 16 ... 12 |
| • for auxiliary contacts | | 2x (24 ... 14) |

Ambient conditions:

| | | |
|-----------------------------|----|-------------|
| Ambient temperature | | |
| • during operation | °C | -25 ... +60 |
| • during storage | °C | -40 ... +80 |
| Derating temperature | °C | 40 |

Protection class IP

IP20

Certificates/ approvals:

General Product Approval

EMC

Test
Certificates



CCC



CSA



UL



C-TICK

[Type Test
Certificates/Test
Report](#)

other

[other](#)

[Declaration of
Conformity](#)

[Environmental
Confirmations](#)

UL/CSA ratings:

yielded mechanical performance [hp] for three-phase
AC motor

• at 220/230 V

— at standard circuit at 50 °C Rated value

metric
hp

2

• at 460/480 V

— at standard circuit at 50 °C Rated value

metric
hp

5

Contact rating of the auxiliary contacts acc. to UL

B300 / R300

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator





<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW30162BB14>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RW30162BB14/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RW30162BB14&lang=en>



last modified:

15.01.2015