

# Isolating transformer TIM 200



Picture shows TIM 100


## Advantages

Safe galvanic isolation
Integrated short-circuit and overload protection
Double output voltage for series or parallel connection
Very good moisture protection and low noise thanks to XtraDenseFill resin encapsulation (up to 300 VA)
Screw terminals under cover with strain relief

## Applications

Isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure in accordance with VDE 0100.

## Sample application



## Standards

Isolating transformer  
to: VDE 0570 Part 2-4, DIN EN 61558-2-4, EN 61558-2-4, IEC 61558-2-4

## Approvals




VDE



# Isolating transformer TIM 200

Type		TIM 200
Electrical data	Input	
	Rated frequency	50 - 60 Hz
	Rated input voltage	230 Vac
	Output	
	Rated output voltage	2 x 115 Vac
	Rated Power	200 VA
	No-load voltage (app. x factor)	1.07
	No-load loss (typ.)	7.40 W
	Efficiency	89.5 %
	Approvals	
Approvals	VDE	
Environment		
Ambient temperature max.	40 °C	
Safety and protection		
Type	Resin encapsulated transformer	
Insulation class	A	
Protection index	IP 20	
Safety class	II	
Short circuit strength	non-inherently short-circuit proof	
Test voltage	5000 Vac, 50 Hz	
Order numbers		
<b>Order Number</b>	<b>TIM 200</b>	

Type		TIM 200
Mechanical data	Terminal and mounting	
	Fixing method	Fixing holes in the terminal connection compartment Screw-type terminals
	Terminals	
	Measures and weights	
	Weight	3.60 kg



Subject to change.