

Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· 1.1 Product identifier

· Trade name: Cold Metal Putty E-COLL

· Article number: 4317784389952, 4317784389969

· 1.2 Relevant identified uses of the substance or mixture and uses advised against

· Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

- · Application of the substance / the mixture Adhesives
- · 1.3 Details of the supplier of the safety data sheet
- · Manufacturer/Supplier:

E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH EDE Platz 1 D-42389 Wuppertal Germany

Tel. +49 202 6096-0 e-mail: sdb@ede.de

- · Further information obtainable from: Product safety department
- · 1.4 Emergency telephone number: Giftinformationszentrum Mainz Tel.: +49 (6131) 19240

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- Classification according to Regulation (EC) No 1272/2008



GHS05 corrosion

Eye Dam. 1 H318 Causes serious eye damage.



GHS09 environment

Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.



Skin Irrit. 2 H315 Causes skin irritation.

Skin Sens. 1 H317 May cause an allergic skin reaction.

(Contd. on page 2)



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 1)

· 2.2 Label elements

· Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms







GHS05 GHS07 GHS09

· Signal word Danger

· Hazard-determining components of labelling:

reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight ≤ 700) 2,4,6-tris(dimethylaminomethyl)phenol

· Hazard statements

H315 Causes skin irritation.

H318 Causes serious eye damage.

H317 May cause an allergic skin reaction.

H411 Toxic to aquatic life with long lasting effects.

· Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.
P264 Wash thoroughly after handling.
P273 Avoid release to the environment.

P280 Wear protective gloves / eye protection / face protection.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if

present and easy to do. Continue rinsing.

P310 Immediately call a POISON CENTER/doctor.

P501 Dispose of contents/container in accordance with local/regional/national/international

regulations.

· 2.3 Other hazards

· Results of PBT and vPvB assessment

PBT: Not applicable.vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation: Mixtures

· Description: Mixture of substances listed below with nonhazardous additions.

- Dangerous components: CAS: 25068-38-6 NLP: 500-033-5 Index number: 603-074-00-8 NLP: 500-033-5 Index numbe



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 2)

CAS: 90-72-2 2,4,6-tris(dimethylaminomethyl)phenol 2.5-10%

Skin Corr. 1B, H314; Acute Tox. 4, H302; Acute Tox. 4, H312; Skin Sens. 1, H317; Aquatic Chronic 3, H412 EINECS: 202-013-9

Index number: 603-069-00-0

· Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- · 4.1 Description of first aid measures
- · General information: Immediately remove any clothing soiled by the product.
- · After inhalation: Supply fresh air.
- · After skin contact:

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

· After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

- · After swallowing: Drink plenty of water and provide fresh air. Call for a doctor immediately.
- · 4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

· 4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- Suitable extinguishing agents:

CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- · For safety reasons unsuitable extinguishing agents: Water with full jet
- · 5.2 Special hazards arising from the substance or mixture

Formation of toxic gases is possible during heating or in case of fire.

Nitrogen oxides (NOx)

Carbon monoxide (CO)

Hydrogen chloride (HCI)

- · 5.3 Advice for firefighters
- · Protective equipment:

Do not inhale explosion gases or combustion gases.

Wear self-contained respiratory protective device.



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 3)

· Additional information

Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

• 6.1 Personal precautions, protective equipment and emergency procedures Ensure adequate ventilation

· 6.2 Environmental precautions:

Inform respective authorities in case of seepage into water course or sewage system. Do not allow product to reach sewage system or any water course. Do not allow to enter sewers/ surface or ground water.

• 6.3 Methods and material for containment and cleaning up: Pick up mechanically.

· 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

- · 7.1 Precautions for safe handling Ensure good ventilation/exhaustion at the workplace.
- · Information about fire and explosion protection: No special measures required.
- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage:
- Requirements to be met by storerooms and receptacles: Store only in the original receptacle.
- · Information about storage in one common storage facility: Not required.
- · Further information about storage conditions: Keep container tightly sealed.
- · Storage class: -
- · 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

· Additional information about design of technical facilities: No further data; see item 7.

(Contd. on page 5)



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 4)

· 8.1 Control parameters

· Ingredients with limit values that require monitoring at the workplace:

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

- · Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- · Personal protective equipment:

· General protective and hygienic measures:

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Avoid contact with the skin.

Avoid contact with the eyes.

Keep away from foodstuffs, beverages and feed.

The usual precautionary measures are to be adhered to when handling chemicals.

- · Respiratory protection: Not necessary if room is well-ventilated.
- · Protection of hands:



Protective gloves

· Material of gloves

Nitrile rubber, NBR Butyl rubber, BR

Recommended thickness of the material: ≥ 0.4 mm

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection:



Tightly sealed goggles

· Body protection: Protective work clothing



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 5)

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form: Solid
Colour: Dark grey
Odour: Nearly odourless
Odour threshold: Not determined.

· **pH-value:** Not applicable.

· Change in condition

Melting point/freezing point: Undetermined. Initial boiling point and boiling range: Undetermined.

· Flash point: > 200 °C

· Flammability (solid, gas): Not determined.

· Decomposition temperature: Not determined.

· Auto-ignition temperature: Product is not selfigniting.

• Explosive properties: Product does not present an explosion hazard.

· Explosion limits:

Lower: Not determined. **Upper:** Not determined.

· Vapour pressure: Not applicable.

• **Density at 20 °C:** 2.18 g/cm³

· Relative density Not determined.

Vapour density Evaporation rate Not applicable. Not applicable.

· Solubility in / Miscibility with

water: Insoluble.

· Partition coefficient: n-octanol/water: Not determined.

· Viscosity:

Dynamic: Not applicable. **Kinematic:** Not applicable.

Organic solvents: 0.0 % VOCV (CH) 0,00 %

(Contd. on page 7)



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 6)

· 9.2 Other information

No further relevant information available.

SECTION 10: Stability and reactivity

- 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided:
 No decomposition if used according to specifications.
- 10.3 Possibility of hazardous reactions Reacts with strong acids and alkali.

Reacts with strong oxidising agents.

- · 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity Based on available data, the classification criteria are not met.
- · Primary irritant effect:
- · Skin corrosion/irritation

Causes skin irritation.

· Serious eye damage/irritation

Causes serious eye damage.

· Respiratory or skin sensitisation

May cause an allergic skin reaction.

- · CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.
- · Reproductive toxicity Based on available data, the classification criteria are not met.
- · STOT-single exposure Based on available data, the classification criteria are not met.
- · STOT-repeated exposure Based on available data, the classification criteria are not met.

(Contd. on page 8)



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 7)

· Aspiration hazard Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- · 12.2 Persistence and degradability No further relevant information available.
- 12.3 Bioaccumulative potential No further relevant information available.
- 12.4 Mobility in soil No further relevant information available.
- · Ecotoxical effects:
- · Remark: Harmful to fish
- · Additional ecological information:
- · General notes:

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water Do not allow product to reach ground water, water course or sewage system. Danger to drinking water if even small quantities leak into the ground. Harmful to aquatic organisms

- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · vPvB: Not applicable.
- 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

· 13.1 Waste treatment methods:

Containers can be recycled if completely empty; if not, dispose product/containers as dangerous waste. Observe local regulations.

· European waste catalogue

08 04 09* waste adhesives and sealants containing organic solvents or other hazardous substances

SECTION 14: Transport information

- · 14.1 UN-Number
- · ADR, IMDG, IATA

UN3077



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 8)

· 14.2 UN proper shipping name

ADR UN-

· IMDG ENVIRONMENTALLY HAZARDOUS SUBSTANCE,

SOLID, N.O.S. (reaction product: bisphenol-A-

(epichlorhydrin) epoxy resin (number average molecular

weight ≤ 700)), MARINE POLLUTANT

· IATA ENVIRONMENTALLY HAZARDOUS SUBSTANCE,

SOLID, N.O.S.

· 14.3 Transport hazard class(es)

· ADR



· Class 9 (M7) Miscellaneous dangerous substances and

articles.

· Label 9

· IMDG, IATA



• Class 9 Miscellaneous dangerous substances and articles.

· Label

14.4 Packing group

· ADR, IMDG, IATA III

• 14.5 Environmental hazards: Product contains environmentally hazardous

substances: reaction product: bisphenol-A-

(epichlorhydrin) epoxy resin (number average molecular

weight \leq 700)

· Marine pollutant: No

Symbol (fish and tree)

Special marking (ADR):
 Special marking (IATA):
 Symbol (fish and tree)

• 14.6 Special precautions for user Warning: Miscellaneous dangerous substances and

articles.

• EMS Number: F-A,S-F

 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable.

(Contd. on page 10)



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 9)

· Transport/Additional information:

· ADR

Limited quantities (LQ)
 Excepted quantities (EQ)
 5 kg
 Code: E1

Maximum net quantity per inner packaging: 30 g Maximum net quantity per outer packaging: 1000 g

· Transport category 3
· Tunnel restriction code E

· IMDG

Limited quantities (LQ)Excepted quantities (EQ)5 kgCode: E1

Maximum net quantity per inner packaging: 30 g Maximum net quantity per outer packaging: 1000 g

· UN "Model Regulation": UN-, -

SECTION 15: Regulatory information

· Directive 2012/18/EU

- · Qualifying quantity (tonnes) for the application of lower-tier requirements 200 t
- · Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t
- · 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Relevant phrases

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

H412 Harmful to aquatic life with long lasting effects.

- · Department issuing SDS: Product safety department
- · Contact: Head of Product Safety Department

Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances



Printing date 06.08.2019 Version number 302 Revision: 09.03.2017

Trade name: Cold Metal Putty E-COLL

(Contd. of page 10)

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOCV: Lenkungsabgabe auf flüchtigen organischen Verbindungen, Schweiz (Swiss Ordinance on volatile organic compounds)

PBT: Persistent, Bioaccumulative and Toxic vPvB: very Persistent and very Bioaccumulative Acute Tox. 4: Acute toxicity - Category 4

Skin Corr. 1B: Skin corrosion/irritation – Category 1B
Skin Irrit. 2: Skin corrosion/irritation – Category 2
Eye Dam. 1: Serious eye damage/eye irritation – Category 1
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

Skin Sens. 1: Skin sensitisation - Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard - Category 2 Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard - Category 3