

FRENCH POLISH

Page: 1

Compilation date: 04/09/2012

Revision No: 4

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: FRENCH POLISH

Product code: FREP

Synonyms: FRENCH POLISH

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd

Waterloo Road Cricklewood London NW2 7TX

United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

1.4. Emergency telephone number

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: F: R11; Xn: R20/21/22; Xn: R68/20/21/22 Classification under CLP: Flam. Liq. 1: H224; STOT SE 2: H371

Most important adverse effects: Highly flammable. Harmful by inhalation, in contact with skin and if swallowed. Harmful:

possible risk of irreversible effects through inhalation, in contact with skin and if

swallowed.

2.2. Label elements

Label elements under CLP:

Hazard statements: H224: Extremely flammable liquid and vapour.

H371: May cause damage to organs .

Signal words: Danger

Hazard pictograms: GHS02: Flame

GHS08: Health hazard





FRENCH POLISH

Page: 2

Precautionary statements: P243: Take precautionary measures against static discharge.

P303+361+353: IF ON SKIN (or hair): Remove immediately all contaminated clothing.

Rinse skin with water.

P264: Wash hands thoroughly after handling.

P280: Wear protective gloves.

P309+311: IF exposed or if you feel unwell: Call a POISON CENTER or doctor.

P370+378: In case of fire: Use carbon dioxide for extinction.

Label elements under CHIP:

Hazard symbols: Highly flammable.

Harmful.





Risk phrases: R11: Highly flammable.

R20/21/22: Harmful by inhalation, in contact with skin and if swallowed.

R68/20/21/22: Harmful: possible risk of irreversible effects through inhalation, in contact

with skin and if swallowed.

Safety phrases: S36/37: Wear suitable protective clothing and gloves.

2.3. Other hazards

PBT: This product is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ETHANOL

EINECS	CAS	CHIP Classification	CLP Classification	Percent
200-578-6	64-17-5	F: R11 Substance with a Community	Flam. Liq. 2: H225	70-90%
		workplace exposure limit.		

METHANOL

200-659-6	67-56-1	F: R11; T: R23/24/25; T:	Flam. Liq. 2: H225; Acute Tox. 3: H331;	1-10%
		R39/23/24/25	Acute Tox. 3: H311; Acute Tox. 3: H301;	
			STOT SE 1: H370	

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove contaminated clothing. Wash skin thoroughly with soap and water. Do NOT

use solvents or thinners. If irritation persists seek medical attention.

Eye contact: Contact lenses should be removed. Irrigate copiously with clean, fresh water for at least

10 minutes, holding the eyelids apart, and seek medical advice.

FRENCH POLISH

Page: 3

Ingestion: Do not induce vomiting. Wash out mouth with water. Get medical attention immediately.
Inhalation: Remove to fresh air, keep the patient warm and at rest. If there is difficulty in breathing, properly trained personnel may administer oxygen. If breathing has stopped, administer artificial respiration (NOT mouth to mouth). Give nothing by mouth if unconscious, place

in the recovery position and seek medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: Irritation. Repeated or prolonged contact may cause defatting of the skin leading to

irritation and dermatitis.

Eye contact: Irritation, reddening and transient corneal damage.

Ingestion: May cause dizziness, loss of coordination, loss of consciousness, temporary or

permanent blindness, coma and death.

Inhalation: There may be irritation of nose, throat and respiratory tract. Dizziness, loss of

coordination, nausea and vomitting may occur.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Water spray, fog or mist. Do NOT use water jet. Carbon dioxide (CO2). Dry chemical

powder. Alcohol resistant foam. Sand or earth.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. May explode in a fire. Solvent vapours may form explosive mixtures

with air. The vapour is heavier than air and may travel along the ground, collect in work pits and cellars, creating a fire and respiratory hazard. Vapour explosion and poison hazard indoors, outdoors and in sewers. In combustion emits toxic fumes of carbon

dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear protective clothing to prevent contact with skin and eyes. Wear self-contained

breathing apparatus. Cool closed containers exposed to fire with water spray. Do NOT

allow run-off from fire fighting to enter drains or water courses.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Ventilate the area. Eliminate all sources of ignition. No Smoking. Avoid inhaling vapour.

The vapour is heavier than air and may collect in confined areas creating a respiratory and explosion hazard. Do not attempt to take action without suitable protective clothing (see section 8). Mark out the contaminated area with signs and prevent access to unauthorised personnel.

FRENCH POLISH

Page: 4

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. If the product enters drains or sewers, the local water company should be contacted immediately. In the case of contamination of streams, rivers or lakes contact the relevant environment agency. Vapour expolsion and poison hazard indoors, outdoors and in sewers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Contain and collect spillages with non-combustible absorbent materials, e.g. sand, earth, vermiculite. Transfer into a suitable container for disposal in accordance with the waste regulations (see section 13) Do not use equipment in clean-up procedure which may produce sparks. Clean preferably with a detergent, avoid the use of solvents.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Avoid inhalation of vapour. Avoid skin and eye contact. Smoking, eating and drinking should be prohibited in areas of storage and use. Emergency shower and eye wash facilities should be readily available. Exclude sources of heat, sparks and open flame. Earth any equipment used in handling. Use non-sparking tools. The Manual Handling Operations Regulations may apply to the handling of containers of this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. Keep away from direct sunlight. Exclude sources of heat, sparks and open flame. Take precautionary measures to prevent product spills into drains, the ground or waters. Further guidance is contained in the HSE guidance note Storage of Flammable Liquids in Containers.

Suitable packaging: Ideally, keep in original container. If transfer is necessary use glass or coated steel

containers. Do NOT store in lead, zinc, tin or aluminium.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ETHANOL

FRENCH POLISH

Page: 5

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL	
UK	1920 mg/m3	-	-	-	
METHANOL					

METHANOL

UK	266 mg/m3	333 mg/m3	-	-
----	-----------	-----------	---	---

8.1. DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Provide adequate ventilation. Where reasonably practicable, this should be achieved by

the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and/or solvent vapours below the relevant occupational exposure limits, suitable respiratory protective equipment should be worn

(see Respiratory protection below).

Respiratory protection: If there is a risk of exposure to high vapour concentrations, use respiratory protective

equipment. All personal protective equipment, including respiratory protective equipment, used to control exposure to hazardous substances must be selected to

meet the requirements of the COSHH Regulations.

Hand protection: Wear Nitrile gloves.

Eye protection: Eye protection designed to protect against liquid splashes should be worn. Ensure eye

bath is to hand.

Skin protection: Overalls are normally suitable, PVC apron if risk of splashing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Brown
Odour: Alcoholic

Solubility in water: Partially miscible.

Viscosity: Non-viscous

Flash point°C: 13 Relative density: 0.875@ 20 C

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

FRENCH POLISH

Page: 6

10.2. Chemical stability

Chemical stability: Stable under normal storage and handling conditions (see Section 7).

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Conditions to avoid: Avoid heat, flames and sparks. Direct sunlight.

10.5. Incompatible materials

Materials to avoid: Strong acids. Strong oxidising agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

ETHANOL

IVN	RAT	LD50	1440	mg/kg
ORL	MUS	LD50	3450	mg/kg
ORL	RAT	LD50	7060	mg/kg

METHANOL

IVN	RAT	LD50	2131	mg/kg
ORL	MUS	LD50	7300	mg/kg
ORL	RAT	LD50	5628	mg/kg

Relevant effects for mixture:

Effect	Route	Basis
Acute toxicity (harmful)	INH DRM ING	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: Irritation. Repeated or prolonged contact may cause defatting of the skin leading to

irritation and dermatitis.

Eye contact: Irritation, reddening and transient corneal damage.

Ingestion: May cause dizziness, loss of coordination, loss of consciousness, temporary or

permanent blindness, coma and death.

Inhalation: There may be irritation of nose, throat and respiratory tract. Dizziness, loss of

coordination, nausea and vomitting may occur.

FRENCH POLISH

Page: 7

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Expected to be biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: Not expected to bioaccumulate.

12.4. Mobility in soil

Mobility: Partially soluble in water. Partially volatile. Partially absorbed into soil. The product should not be allowed to enter drains or water courses or be deposited where it can affect ground or surface waters.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT substance.

12.6. Other adverse effects

Other adverse effects: It is unlikely this material will present an environmental hazard.

Section 13: Disposal considerations

13.1. Waste treatment methods

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No Marine pollutant: No

14.6. Special precautions for user

Section 15: Regulatory information

FRENCH POLISH

Page: 8

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: Saftey Data Sheet complies with UK regulatory references in accordance with CHIP 3.1.

Section 16: Other information

Other information

Other information: The product complies with the requirements of the Toy Safety Regulations, BS EN 71

Part 3 1995. A certificate of conformity can be supplied upon request.

Phrases used in s.2 and 3: H224: Extremely flammable liquid and vapour.

H225: Highly flammable liquid and vapour.

H301: Toxic if swallowed.

H311: Toxic in contact with skin.

H331: Toxic if inhaled.

H370: Causes damage to organs <or state all organs affected, if known> <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

H371: May cause damage to organs <or state all organs affected, if known> <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

R11: Highly flammable.

R20/21/22: Harmful by inhalation, in contact with skin and if swallowed.

R23/24/25: Toxic by inhalation, in contact with skin and if swallowed.

R39/23/24/25: Toxic: danger of very serious irreversible effects through inhalation, in contact with skin and if swallowed.

R68/20/21/22: Harmful: possible risk of irreversible effects through inhalation, in contact with skin and if swallowed.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product. As the specific conditions of use of the product are outside the supplier's control, the user is responsible for ensuring that the requirements of relevant legislation are complied with.