

Stereo microscope modular system - Universal stands KERN OZB-UE







OZB-A1203







OZB-A1211



OZB-A1213



OZB-A6303



OZB-A6301

Individuality, variety and flexible working through our modular construction system ► ECO universal stands

Features

- · With our universal stands and basic stands, as well as microscope heads and external illumination units, you can configure your microscope to your own specifications and adapt it to your application
- · Thanks to the versatile, adjustable universal stands it is possible to work in the very best way in all areas with the most varied of samples
- · Small universal stands are available as stand base variants as well as with the option of a clamp for the edge of a bench. Depending on the model, you have the choice of a telescopic arm stand or a telescopic double arm universal stand with ball bearings
- The spring loaded universal stands including bench clamp will make your daily work with your stereo microscope easier. Now including coarse adjustment knob for easy, flexible focussing

Technical data

OZB-A1201/OZB-A1211

- · Column height: 430 mm
- · Length telescopic arm: 385 mm

OZB-A1203/OZB-A1213

- · Column height: 430 mm
- · Length telescopic arm: 480 mm

OZB-A6302

- · Height spring loaded arm: 525 mm
- · Length spring loaded arm: 620 mm

OZB-A6301

· Column height: 300 mm

OZB-A6303

- · Height spring loaded arm: 400 mm
- · Length spring loaded arm: 850 mm

Model Description

KERN

OZB-A1201	Telescopic arm - Plate - excl. holder
OZB-A1211	Telescopic arm - Clamp Edge of bench (Range: max. 40 mm) - excl. holder
OZB-A1203	Jointed arm - Plate - excl. holder
OZB-A1213	Jointed arm - Clamp Edge of bench (Range: max. 40 mm) - excl. holder
OZB-A6302	Spring loaded arm (Pneumatic spring) - Clamp (Range: max. 50 mm) - with holder (Coarse focusing knob)
OZB-A6303	Spring loaded arm (Compression spring) - Clamp (Range: max. 50 mm) - with holder (Coarse focusing knob)
OZB-A6301	Pillar style stand with "C"-shape base – excl. holder
OZB-A6302 OZB-A6303	Spring loaded arm (Pneumatic spring) – Clamp (Range: max. 50 mm) – with holder (Coarse focusing knob) Spring loaded arm (Compression spring) – Clamp (Range: max. 50 mm) – with holder (Coarse focusing knob)

MICROSCOPES & REFRACTOMETERS 2023

KERN PICTOGRAMS





360° rotatable microscope head



Monocular Microscope For the inspection with one eye



Binocular Microscope For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



LED illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes



Fluorescence illumination for compound microscopes

With 100 W mercury lamp and filter



Fluorescence illumination **for compound microscopes**With 3 W LED illumination and filter



Phase contrast unit

For a higher contrast



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light

00

Infinity system

Infinity corrected optical system



Zoom magnification

For stereomicroscopes



Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card

For data storage



USB 2.0 digital camera

For direct transmitting of the picture to a PC



USB 3.0 digital camera

For direct transmitting of the picture to a PC



WIFI data interface:

For transmitting of the picture to a mobile display device



HDMI digital camera

For direct transmitting of the picture to a display device



PC software

To transfer the measurements from the device to a PC.



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water

splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

ABBREVIATIONS

C-Mount Adapter for the connection of a camera to a trinocular microscope

FPS Frames per second

High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses) H(S)WF

LWD Long Working Distance N.A. **Numerical Aperture** SLR camera Single-Lens Reflex camera

SWF Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

W.D. Working Distance

WF Wide Field (Field number up to Ø 22 mm for 10× eyepiece) Battery operation rechargeable Prepared for a rechargeable battery



■→)

RECHARGE

BATT

operation

Battery operation

Plug-in power supply 230V/50Hz in standard version for EU. On request GB, AUS or USA version.

Ready for battery operation. The battery

type is specified for each device.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.