

Core drill HSS
for universal use up to 1000 N/mm²



Application

For core drilling pre-drilled, pre-cast or punched holes.

Version

- 3-blade design

Advantage

- stable grinding combined with the three blades ensure that any mis-alignments and run-out of the pre-made holes are corrected

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	22	20	10	6	4	40	50	40	35	30	25	40		20					

Art. No.	11410 060
Cutting material	HSS
Number of cutting edges	3 PCS
Type	Type N
Cutting edge diameter	6.00 mm
Cutting edge length	80 mm
Length	116 mm
f steel 700	0.06 mm/U
DIN	344

EAN-Code

4050293010404