

Part number:
63902-0202

Copyright

© 2013, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

May 22, 2013, 12:29 AM

Corporate Headquarters

FLIR Systems, Inc.
27700 SW Parkway Ave.
Wilsonville, OR 97070
USA
Telephone: +1-503-498-3547

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Legal disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply.

Information and equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited.

FLIR Commercial Systems B.V.

Charles Petitweg 21
4847 NW Breda
The Netherlands
Phone: +31 (0) 765 79 41 94
Fax: +31 (0) 765 79 41 99
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Systems Sweden

Phone: +46 (0)8 753 25 00
Fax: +46 (0)8 753 23 64
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Systems Germany

Phone: +49 (0)69 95 00 900
Fax: +49 (0)69 95 00 9040
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Advanced Thermal Solutions France

Phone: +33 (0)1 60 37 01 00
Fax: +33 (0)1 64 11 37 55
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Systems UK

Phone: +44 (0) 1732 220 011
Fax: +44 (0) 1732 220 014
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Systems Italy

Phone: +39 (0)2 99 45 10 01
Fax: +39 (0)2 99 69 24 08
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Systems Spain

Phone: +34 91 490 40 60
Fax: +34 91 662 97 48
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Systems Middle East

Phone: +971 4 299 6898
Fax: +971 4 299 6895
E-mail: flir@flir.com
Web: <http://www.flir.com>

FLIR Systems Belgium

Phone: +32 (0)3 287 87 10
Fax: +32 (0)3 287 87 29
E-mail: flir@flir.com
Web: <http://www.flir.com>



Imaging and optical data

IR resolution	160 × 120 pixels
MSX resolution	320 × 240 pixels
Thermal sensitivity/NETD	<0.06°C (0.11°F) / <60 mK
Field of view (FOV)	45° × 34°
Minimum focus distance	0.5 m (1.6 ft.)
Spatial resolution (IFOV)	5.2 mrad
Image frequency	9 Hz
Focus	Focus free

Detector data

Detector type	Focal plane array (FPA), uncooled microbolometer
Spectral range	7.5–13 μm

Image presentation

Display	3.0 in. 320 x 240 color LCD
Image adjustment	Automatic adjust/lock image

Image presentation modes

Image modes	IR image, visual image, MSX, picture in picture, thumbnail gallery
Multi Spectral Dynamic Imaging (MSX)	IR image with enhanced detail presentation
Picture in Picture	IR area on visual image

Measurement

Object temperature range	-20°C to +250°C (-4°F to +482°F)
Accuracy	±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (+50°F to 95°F) and object temperature above +0°C (+32°F)

Measurement analysis

Spotmeter	Center spot
Area	Box with max./min.
Emissivity correction	Variable from 0.1 to 1.0
Emissivity table	Emissivity table of predefined materials
Reflected apparent temperature correction	Automatic, based on input of reflected temperature

Alarm

Color alarm	Blue below or red above set temperature
-------------	---

P/N: 63902-0202

© 2013, FLIR Systems, Inc.
All rights reserved worldwide.

Set-up	
Color palettes	Black and white, iron and rainbow
Set-up commands	Local adaptation of units, language, date and time formats
Storage of images	
Image storage capacity	Internal memory store at least 500 sets of images
Image storage mode	Simultaneous storage of images in IR, visual and MSX
File formats	Standard JPEG, 14-bit measurement data included
Data communication interfaces	
Interfaces	USB Micro: Data transfer to and from PC and Mac device
Power system	
Battery type	Rechargeable Li Ion battery
Battery voltage	3.7 V
Battery operating time	Approx. 4 hours at +25°C (+77°F) ambient temperature and typical use
Charging system	Battery is charged inside the camera or in specific charger.
Charging time	2.5 hours to 90% capacity in camera. 2 hours in charger.
Power management	Automatic shut-down
AC operation	AC adapter, 90–260 VAC input, 5 VDC output to camera
Environmental data	
Operating temperature range	–15°C to +50°C (+5°F to +122°F)
Storage temperature range	–40°C to +70°C (–40°F to +158°F)
Humidity (operating and storage)	IEC 60068-2-30/24 h 95% relative humidity
EMC	<ul style="list-style-type: none"> • WEEE 2012/19/EC • RoHs 2011/65/EC • C-Tick • EN 61000-6-3 • EN 61000-6-2 • FCC 47 CFR Part 15 Class B
Encapsulation	IP 54 (IEC 60529)
Bump	25 g (IEC 60068-2-29)
Vibration	2 g (IEC 60068-2-6)
Drop	2 m (6.6 ft.)
Physical data	
Camera weight, incl. battery	0.575 kg (1.27 lb.)
Camera size (L x W x H)	244 x 95 x 140 mm (9.6 x 3.7 x 5.5 in.)
Color	Black and gray
Certifications	
Certification	UL, CSA, CE, PSE and CCC
Shipping information	
Packaging, type	Hard case
	<ul style="list-style-type: none"> • Infrared camera • Hard transport case • Battery (inside camera) • USB cable • Power supply/charger with EU, UK, US and Australian plugs • User documentation CD-ROM • Printed documentation • FLIR Tools download card
Packaging, weight	2.7 kg (5.95 lb.)
Packaging, size	303 x 206 x 128 mm (11.9 x 8.1 x 5.0 in.)
EAN-13	4743254001008
UPC-12	845188004958



P/N: 63902-0202

© 2013, FLIR Systems, Inc.
All rights reserved worldwide.

Shipping information

Country of origin

Estonia

TO BE RELEASED