



















Amp	Volt	Hz	IP Ident. colour + h	Part No.	Wall socket outlets 3 P + N +  IEC/EN 60 309	 9	EAN-No. 4015609...																																												
					external fixing means, 1 top cable entry																																														
																																																			
16	400	50/60	6	110		10/60	000012 009091 009138 009152																																												
	110	50/60	4	110 504																																															
	230	50/60	9	110 509																																															
	440	60	11	110 511																																															
32	400	50/60	6	130		10/60	000081 010585 010622 010646																																												
	110	50/60	4	130 504																																															
	230	50/60	9	130 509																																															
	440	60	11	130 511																																															
																																																			
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>l</th> <th>n</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>60</td> <td>5,3</td> <td>80</td> <td>74</td> <td>90</td> <td>31</td> <td>129</td> <td>16</td> </tr> <tr> <td>32 A</td> <td>60</td> <td>5,3</td> <td>97</td> <td>82</td> <td>105</td> <td>45</td> <td>155</td> <td>21</td> </tr> </tbody> </table>	Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	90	31	129	16	32 A	60	5,3	97	82	105	45	155	21																			
Ampère	b	c	d	e	f	l	n	Pg																																											
16 A	60	5,3	80	74	90	31	129	16																																											
32 A	60	5,3	97	82	105	45	155	21																																											
					red special version, external fixing means, 1 top cable entry																																														
																																																			
16	400	50/60	6	113		10/60	000036																																												
	230	50/60																																																	
32	400	50/60	6	133		10/60	000104																																												
	230	50/60																																																	
																																																			
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>l</th> <th>n</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>60</td> <td>5,3</td> <td>80</td> <td>74</td> <td>90</td> <td>31</td> <td>129</td> <td>16</td> </tr> <tr> <td>32 A</td> <td>60</td> <td>5,3</td> <td>97</td> <td>82</td> <td>105</td> <td>45</td> <td>155</td> <td>21</td> </tr> </tbody> </table>	Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	90	31	129	16	32 A	60	5,3	97	82	105	45	155	21																			
Ampère	b	c	d	e	f	l	n	Pg																																											
16 A	60	5,3	80	74	90	31	129	16																																											
32 A	60	5,3	97	82	105	45	155	21																																											
					internal fixing means, 2 cable entries both, top and bottom (knock-out)																																														
																																																			
16	400	50/60	6	111		5	000029 009411 009435 009459																																												
	110	50/60	4	111 504																																															
	230	50/60	9	111 509																																															
	440	60	11	111 511																																															
32	400	50/60	6	131		5	000098 010837 010844 010851																																												
	110	50/60	4	131 504																																															
	230	50/60	9	131 509																																															
	440	60	11	131 511																																															
																																																			
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>l</th> <th>n</th> <th>v</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>66,5</td> <td>5</td> <td>96</td> <td>95</td> <td>146</td> <td>47,5</td> <td>164</td> <td>7</td> <td>16/21</td> </tr> <tr> <td>32 A</td> <td>66,5</td> <td>5</td> <td>96</td> <td>95</td> <td>157</td> <td>47,5</td> <td>173</td> <td>7</td> <td>16/21</td> </tr> </tbody> </table>	Ampère	b	c	d	e	f	l	n	v	Pg	16 A	66,5	5	96	95	146	47,5	164	7	16/21	32 A	66,5	5	96	95	157	47,5	173	7	16/21																
Ampère	b	c	d	e	f	l	n	v	Pg																																										
16 A	66,5	5	96	95	146	47,5	164	7	16/21																																										
32 A	66,5	5	96	95	157	47,5	173	7	16/21																																										
					internal fixing means, cable entries: 1 x top (open), 2 x bottom (knock-out) and vice versa																																														
63	400	50/60	6	161		2	000159 011407 011438 011452																																												
	110	50/60	4	161 504																																															
	230	50/60	9	161 509																																															
	440	60	11	161 511																																															
125	400	50/60	6	163		2	251162 251179 251186 251193																																												
	110	50/60	4	163 504																																															
	230	50/60	9	163 509																																															
	440	60	11	163 511																																															
																																																			
																																																			
					<table border="1"> <thead> <tr> <th>Part</th> <th>Ampère</th> <th>a</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>n</th> <th>v</th> <th>Pg</th> <th>Part</th> <th>Amp.</th> <th>a</th> <th>b</th> <th>b1</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>n</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>161</td> <td>63 A</td> <td>136</td> <td>104</td> <td>4,2</td> <td>172</td> <td>121</td> <td>178</td> <td>220</td> <td>5</td> <td>29</td> <td>163</td> <td>63 A</td> <td>183</td> <td>151</td> <td>114</td> <td>6,5</td> <td>237</td> <td>183</td> <td>196</td> <td>302</td> <td>21/29</td> </tr> </tbody> </table>	Part	Ampère	a	b	c	d	e	f	n	v	Pg	Part	Amp.	a	b	b1	c	d	e	f	n	Pg	161	63 A	136	104	4,2	172	121	178	220	5	29	163	63 A	183	151	114	6,5	237	183	196	302	21/29		
Part	Ampère	a	b	c	d	e	f	n	v	Pg	Part	Amp.	a	b	b1	c	d	e	f	n	Pg																														
161	63 A	136	104	4,2	172	121	178	220	5	29	163	63 A	183	151	114	6,5	237	183	196	302	21/29																														

see page 2/20