



Figure similar

TRANSFORMER SITAS; PHASES:1;  
 PN/PN(S6)(KVA):0,063 /0,19; UPRI(V):440+/-5%;  
 USEC(V):110; ISEC(A):0,57; F(HZ):50...60; VECTOR  
 GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B; IP00; TYPE  
 OF TERMINALS:SCREW/TAB CONNECTION;  
 INSTALLATION:SCREWS/MOUNTING RAILS; EN  
 61558-2-1, -2-2, -2-4 >UL/CSA-RECOGNIZED<  
 >CONTROL CIRCUIT TRANSFORMER< >ISOLATION  
 TRANSFORMER<

### General technical data:

<b>Product designation</b>		transformer SITAS
<b>product brand name</b>		SIDAC
<b>Operating apparent output Rated value</b>	V·A	63
<b>Efficiency</b>		0.85
<b>Connection method for transformers</b>		II0
<b>Certificate of suitability</b>		CE / cRUus
<b>Product function</b>		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
<b>Number of shielding windings</b>		0
<b>Short-term vector power</b>	V·A	190

### Inputs:

<b>Phase number of the inputs</b>		1
<b>Input voltage</b>		
• _1 Rated value	V	462
• _2 Rated value	V	440
• _3 Rated value	V	418
<b>Electrical input frequency</b>		
• minimum	Hz	50
• maximum	Hz	60

### Outputs:

<b>Phase number of the outputs</b>		1
------------------------------------	--	---

<b>Output voltage</b>		
<ul style="list-style-type: none"> <li>• _1 Rated value</li> </ul>	V	110
<b>Electrical output frequency</b>		
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	Hz	60
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	Hz	50

#### Ambient conditions:

<b>Thermal class acc. to IEC 60085</b>		B
<b>Ambient temperature Rated value</b>	°C	40
<b>Protection class IP</b>		IP00

#### Mechanical data:

<b>Type of electrical connection</b>		
<ul style="list-style-type: none"> <li>• at output for main current circuit</li> </ul>		screw-type terminals / tab terminals
<ul style="list-style-type: none"> <li>• at input for main current circuit</li> </ul>		screw-type terminals / tab terminals
<b>Mounting type</b>		screws / standard rail
<b>Construction form of the iron core</b>		EI 84/28
<b>Width</b>	m	0.086
<b>Height</b>	m	0.098
<b>Depth</b>	m	0.09

#### Certificates/ approvals:

General Product Approval	Shipping Approval	other
		
		<a href="#">other</a>

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM32425CJ100FA0>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM32425CJ100FA0>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AM32425CJ100FA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM32425CJ100FA0&lang=en)

last modified:

15.01.2015