



## Model Number

**LME 18-1,9-1,0-K9**

Glass fiber optic - thru-beam with metal covering

## Features

- Sturdy metallic version
- Chemical-resistant

## Series

### Fiber optic amplifiers

Device series	VL18LL VariKont M
---------------	----------------------

## Description

### Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



## Technical data

### General specifications

Fiber optic length	l	1000 mm
Fiber optic diameter	d	5 mm
Adapter form		18
End piece		Cylindrical right angle
Bending radius		min. 20 mm
Fiber bundle diameter		1.9 mm

### Ambient conditions

Ambient temperature	-20 ... 85 °C (-4 ... 185 °F) [Adapter]
	-50 ... 200 °C (-58 ... 392 °F) [End head and Covering]
Storage temperature	-20 ... 85 °C (-4 ... 185 °F)

### Mechanical specifications

Protection degree	IP40
Material	
Optical face	glass
Sheathing	metal
Core	Glass fiber
End piece	Stainless steel 1.4305 / AISI 303
Adapter	PBT
Extraction force	120 N

## Dimensions

