


Fuse holder terminal blocks for fuses 5x20 mm .197x.787 in. and 5x25 mm .197x.984 in.

Screw clamp  DIN 1 - DIN3

M 4/8.SF- 4 mm² blocks - 8 mm .315" spacing



M 4/8.SF

Characteristics

		IEC NFC DIN	UL	CSA
Wire size mm ² / AWG	Solid	0.5 - 6	22-12 AWG	22-12 AWG
	Stranded	0.5 - 4		
Voltage	V	630 (1)(2)	600 (1)	250
Current	A	6.3	10	10
Rated wire size	mm ² / AWG	4 mm ²	12 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .37"		
Recommended torque	Nm / lb.in	0.5-0.8 Nm / 4.4-7.1 lb.in		


(1) Insulation voltage of terminal block - operating voltage : according to fuse.

(2) 400 V for block M 4/6.SFT

Selection

Description	Type	Order P/N	Packaging	Weight kg
Standard block grey	<input type="checkbox"/> M 4/8.SF	1SNA 115 657 R2500	50	
Block with test socket Ø2 mm grey	<input type="checkbox"/> M 4/8.SF	1SNA 115 662 R2200	50	
Standard block orange	<input type="checkbox"/> M 4/8.SF2	1SNA 105 135 R1100	50	
Standard block beige V0	<input type="checkbox"/> M 4/8.SF.V0	1SNA 195 657 R2600	50	

M 4/8.SFL - 4 mm² blocks - 8 mm .315" spacing



M 4/8.SFL


Characteristics

		IEC NFC DIN	UL	CSA
Wire size mm ² / AWG	Solid	0.5 - 6	22-12 AWG	22-12 AWG
	Stranded	0.5 - 4		
Voltage	V	400	600	250
Current	A	6.3	10	10
Rated wire size	mm ² / AWG	4 mm ²	12 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .374"		
Recommended torque	Nm / lb.in	0.5-0.8 Nm / 4.4-7.7 lb.in		

Selection

Description	Type	Order P/N	Packaging	Weight kg
Block with fusion indicator neon grey	<input type="checkbox"/> M 4/8.SFL	1SNA 115 661 R2100	50	
Block with fusion indicator 24V grey	<input type="checkbox"/> M 4/8.SFD	1SNA 115 663 R2300	50	

M 4/8.SN - 4 mm² blocks - 8 mm .315" spacing



M 4/8.SN

Characteristics

		IEC NFC DIN	UL	CSA
Wire size mm ² / AWG	Solid	0.5 - 6	22-12 AWG	24-12 AWG
	Stranded	0.5 - 4		
Voltage	V	630 (1)	600	250
Current	A	6.3	10	10
Rated wire size	mm ² / AWG	4 mm ²	12 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .37"		
Recommended torque	Nm / lb.in	0.5-0.8 Nm / 4.4-7.1 lb.in		

(1) Insulation voltage of terminal block - operating voltage : according to fuse.

Selection

Description	Type	Order P/N	Packaging	Weight kg
Standard block grey body/blue grip	<input type="checkbox"/> M 4/8.SN	1SNA 115 659 R0700	50	
Standard block beige body/blue V0 grip	<input type="checkbox"/> M 4/8.SN.V0	1SNA 195 659 R0000	50	

Accessories

End stop	BAM	9.1 mm	1SNA 103 002 R2600	50	
End section	grey	<input type="checkbox"/> FEM8S	1.5 mm	1SNA 116 951 R1500	20
	orange	<input type="checkbox"/> FEM8S	1.5 mm	1SNA 103 923 R1500	20



BAM



FEM8S