

DATA SHEET

AUTOMOTIVE GRADE SURGE CHIP RESISTORS

SR series

20%, 10%, 5% 1%, 0.5%

sizes 0201/0402/0603/0805/1206/1210/1218/2010/2512 RoHS compliant & Halogen free



YAGEO



SCOPE

This specification describes SR0201 to SR2512 chip resistors with lead-free terminations made by thick film process.

APPLICATIONS

- Telecommunications
- Power supplies
- Car electronics

FEATURES

- AEC-Q200 qualified
- Superior to RC series in pulse withstanding voltage and surge withstanding voltage.
- MSL class: MSL I
- Halogen free epoxy
- RoHS compliant
 - Products with lead-free terminations meet RoHS requirements
 - Pb-glass contained in electrodes, resistor element and glass are exempted by RoHS
- Reduce environmentally hazardous waste
- High component and equipment reliability

ORDERING INFORMATION - GLOBAL PART NUMBER

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

SR XXXX X X X XX XXXX L

(1) (2) (3) (4) (5) (6) (7)

(I) SIZE

0201 / 0402 / 0603 / 0805 / 1206 / 1210 / 1218 / 2010 / 2512

(2) TOLERANCE

 $D = \pm 0.5\%$

 $F = \pm 1\%$

 $| = \pm 5\%$

 $K = \pm 10\%$

 $M = \pm 20\%$

(3) PACKAGING TYPE

R = Paper taping reel

K = Embossed taping reel

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

- = Based on spec.

(5) TAPING REEL & POWER

07 = 7 inch dia. Reel & Standard power

7W = 7 inch dia. Reel & 2 x standard power 7T = 7 inch dia. Reel & 3 x standard power

13 = 13 inch dia, Reel

47 = 7 inch dia, Reel & 4xstandard power

(6) RESISTANCE VALUE

 $I \Omega \le R \le IM \Omega$

There are $2\sim4$ digits indicated the resistance value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. I K2, not I K20.

Detailed coding rules of resistance are shown in the table of "Resistance rule of global part number".

(7) DEFAULT CODE

Letter L is the system default code for ordering only. (Note)

Resistance rule of global part				
Resistance coding rule	Example			
XRXX (1 to 9.76 Ω)	IR = I Ω $IR5 = I.5 Ω$ $9R76 = 9.76 Ω$			
XXRX (10 to 97.6 Ω)	$10R = 10 \Omega$ $97R6 = 97.6 \Omega$			
XXXR (100 to 976 Ω)	100R = 100 Ω			
XKXX (1 to 9.76 K Ω)	IK = I,000 Ω 9K76 = 9760 Ω			
XXKX (10 to 97.6 KΩ)	$10K = 10,000 \Omega$ 97K6= 97,600 Ω			
XXXK (100 KΩ)	100K = 100,000 Ω			

ORDERING EXAMPLE

The ordering code for an SR0805 chip resistor, value $10~\text{K}\Omega$ with $\pm 5\%$ tolerance, supplied in 7-inch tape reel is: SR0805JR-0710KL.

0201/0402/0603/0805/1206/1210/1218/2010/2512

MARKING

SR0201 / SR0402



No Marking

Fig. I

SR1218



E-24 series: 3 digits

First two digits for significant figure and 3rd digit for number of zeros

Fig. 2 Value=10 KΩ

SR0603 / SR0805 / SR1206 / SR1210 / SR2010 / SR2512



E-24 series: 3 digits

First two digits for significant figure and 3rd digit for number of zeros

NOTE

For further marking information, please refer to data sheet "Chip resistors marking".

TAPING REEL & POWER

Table I

		POWER	, W (P70)	
TYPE		COI	DING	
0	7	7W	7T	47
0201 L	/20	1/10	-	1/5
0402 L	/16	1/8	1/5	-
0603 L	/10	1/5	1/4	1/3
0805 L	/8	1/4	1/3	1/2
1206 L	/4	1/2	3/4	1
1210 L	/2	1	=	=
1218		1.5	=	=
2010 3	3/4	1.25	-	-
2512		2	=	





CONSTRUCTION

YAGEO

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive glaze. The resistive glaze is covered by a lead-free glass. The composition of the glaze is adjusted to give the approximately required resistance value. The whole element is covered by a protective overcoat. The top of overcoat is marked with the resistance value. Finally, the two external terminations (Ni/matte tin) are added, as shown in Fig.4.

OUTLINES






<u>DIMENSIONS</u>

Table 2

TYPE	L (mm)	W (mm)	H (mm)	I ₁ (mm)	I ₂ (mm)
SR0201	0.60±0.03	0.30±0.03	0.23±0.03	0.12±0.05	0.15±0.05
SR0402	1.00±0.05	0.50±0.05	0.35±0.05	0.20±0.10	0.25±0.10
SR0603	1.60±0.10	0.80±0.10	0.45±0.10	0.25±0.15	0.25±0.15
SR0805	2.00±0.10	1.25±0.10	0.50±0.10	0.35±0.20	0.35±0.20
SR1206	3.10±0.10	1.60±0.10	0.55±0.10	0.45±0.20	0.45±0.20
SR1210	3.10±0.10	2.60±0.15	0.55±0.10	0.45±0.15	0.50±0.20
SR1218	3.10±0.10	4.60±0.10	0.55±0.10	0.45±0.20	0.40±0.20
SR2010	5.00±0.10	2.50±0.15	0.55±0.10	0.55±0.15	0.55±0.20
SR2512	6.35±0.10	3.10±0.15	0.55±0.10	0.60±0.20	0.60±0.20





YAGEO

ELECTRICAL CHARACTERISTICS

Table 3

lable 3	CHARACTERISTICS						
TYPE	POWER	resistance range	Operating Temperature Range	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Temperature Coefficient of Resistance
SR0201	1/20W 1/10W 1/5W		-	25 V	50 V	50 V	$I\Omega \le R < I0\Omega$ $I00 \sim +350 \text{ ppm}^{\circ}\text{C}$ $I0\Omega \le R \le IM\Omega$ $\pm 200 \text{ ppm}^{\circ}\text{C}$
SR0402	1/16W 1/8W 1/5W			75 V	100 V	100 V	
SR0603	1/10W 1/5W 1/4W 1/3W			150V	300V	300V	
SR0805	1/8 W 1/4W 1/3W	E24/E96 0.5%, 1% E24 5%, 10%, 20%	–55 °C to +155 °C -	500V	1000V	1000V	$10\Omega \le R \le 1M\Omega$
SR1206	1/2W 1/4 W 1/2W 3/4W	$ \Omega \le R \le M \Omega $		200 V	400 V	500 V	$\pm 100 \text{ ppm/ °C}$ $1\Omega \le R < 10\Omega$ $\pm 200 \text{ ppm/ °C}$
SR1210	1/2W			200 V	400 V	500 V	
SR1218	1.5W			200 V	400 V	500 V	
SR2010	3/4W 1.25W			200 V	400 V	500 V	
SR2512	1 W 2W			500 V	1000 V	1000 V	

FOOTPRINT AND SOLDERING PROFILES

Recommended footprint and soldering profiles, please refer to data sheet "Chip resistors mounting".

PACKING STYLE AND PACKAGING QUANTITY

Table 4 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION	SR0201/0402	SR0603/0805/1206	SR1210	SR1218/2010/2512
Paper taping reel (R)	7" (178 mm)	10,000	5,000	5,000	
	13" (330 mm)	50,000	20,000	20,000	
Embossed taping reel (K)	7" (178 mm)				4,000

NOTE

1. For paper/embossed tape and reel specification/dimensions, please refer to data sheet "Chip resistors packing".

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

Range: -55 °C to +155 °C

POWER RATING

Each type rated power at 70 °C: SR0201: 1/20W, 1/10W, 1/5W SR0402: 1/16W, 1/8W, 1/5W

SR0603: 1/10W, 1/5W, 1/4W, 1/3W SR0805: 1/8W, 1/4W, 1/3W, 1/2W SR1206: 1/4W, 1/2W, 3/4W, 1W

SR1210: 1/2W, 1W SR1218: 1W, 1.5W SR2010: 3/4W, 1.25W SR2512: 1W, 2W

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:


$$V = \sqrt{(P \times R)}$$

or max. working voltage whichever is less $\ensuremath{\mathsf{Where}}$


V = Continuous rated DC or AC (rms) working voltage (V)


P = Rated power (W)

 $R = Resistance value (\Omega)$




Pulse load Behavior








Pulse load Behavior







TESTS AND REQUIREMENTS

___Table 5 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
High Temperature	AEC-Q200 Test 3	1,000 hours at $T_A = 155$ °C, unpowered	$\pm (2.0\% + 0.05\Omega)$ for D/F tol
Exposure	MIL-STD-202 Method 108		$\pm (3.0\% {+} 0.05 \Omega)$ for others
Moisture Resistance	MIL-STD-202 Method 106	Each temperature / humidity cycle is defined at	$\pm (0.5\% + 0.05\Omega)$ for D/F tol
		8 hours, 3 cycles / 24 hours for 10d. with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered	$\pm (2.0\% {+} 0.05 \Omega)$ for others
Biased	AEC-Q200 Test 7	1,000 hours; 85 °C / 85% RH	$\pm (1.0\% + 0.05\Omega)$ for D/F tol
Humidity	MIL-STD-202 Method 103	10% of operating power	$\pm (3.0\% + 0.05\Omega)$ for others
		Measurement at 24±4 hours after test conclusion.	
Operational Life	AEC-Q200 Test 8	1,000 hours at 125 °C, derated voltage applied	$\pm (2.0\% + 0.05\Omega)$ for D/F tol
	MIL-STD-202 Method 108	for 1.5 hours on, 0.5 hour off, still-air required	$\pm(3.0\% {\pm} 0.05\Omega)$ for others
Resistance to	AEC-Q200 Test 15	Condition B, no pre-heat of samples	±(1.0%+0.05Ω)
Soldering Heat	MIL-STD-202 Method 210	Lead-free solder, 260 \pm 5 °C, 10 \pm 1 seconds immersion time	No visible damage
		Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	
Thermal Shock	MIL-STD-202 Method 107	-55/+125 °C	$\pm (0.5\% + 0.05\Omega)$ for D/F tol
		Number of cycles is 300. Devices mounted	$\pm (1.0\% {+} 0.05 \Omega)$ for others
		Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	
ESD	AEC-Q200 Test 17	Human Body Model,	±(3.0%+0.05Ω)
	AEC-Q200-002	I pos. + I neg. discharges	
		0201: 500V	
		0402/0603: IKV	
		0805 and above: 2KV	
Solderability	AEC-Q200 Test 18	Electrical Test not required Magnification 50X	Well tinned (≥95% covered)
- Wetting	J-STD-002	SMD conditions:	No visible damage
		(a) Method B, aging 4 hours at 155 °C dry heat, dipping at 235±3 °C for 5±0.5 seconds.	No visiole dall'idge
		(b) Method B, steam aging 8 hours, dipping at $215\pm3~^{\circ}\text{C}$ for 5 ± 0.5 seconds.	
		(c) Method D, steam aging 8 hours, dipping at 260±3 °C for 30±0.5 seconds.	



 Chip Resistor Surface Mount
 SR
 SERIES
 0201/0402/0603/0805/1206/1210/1218/2010/2512

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Board Flex	AEC-Q200 Test 21 AEC-Q200-005	Chips mounted on a 100mm x 40mm glass epoxy resin PCB (FR4)	±(1.0%+0.05Ω)
		Bending for 0201/0402: 5 mm 0603/0805: 3 mm 1206 and above: 2 mm	
		Holding time: minimum 60 seconds	
Temperature Coefficient of Resistance (T.C.R.)	MIL-STD-202 Method 304	At +25/–55 °C and +25/+125 °C Formula: T.C.R= $\frac{R_2-R_1}{R_1(t_{2S}-t_1)} \times 10^6 \text{ (ppm/°C)}$	Refer to table 2
		Where t_1 =+25 °C or specified room temperature t_2 =-55 °C or +125 °C test temperature R_1 =resistance at reference temperature in ohms R_2 =resistance at test temperature in ohms	
Short Time Overload	IEC60115-1 8.1	2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature	±(2.0%+0.05Ω)



REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 12	Apr. 23, 2024	-	- Add continuous pulse curve
Version II	Aug. 31, 2023	-	- Upgrade the working voltage of 2512 to 500V
			- Merge F/D tol
			Add size 0201
Version 10	Aug. 02, 2022		Upgrade the working voltage of 0402 to 75V
VEISION 10	Aug. 02, 2022	-	Upgrade the working voltage of 0603 to 150V
			Upgrade the working voltage of 0805 to 500V
			12 dimension updated, for size 1206, size 2010, size 2512
Version 9	Aug. 04, 2021	-	- Upgrade to Automotive Grade
Version 8	Jul. 22, 2019	-	- Update power rating
		- Extend resistance range of 0402 ~ 2512 to 1Mohm,	
Version 7	C 27 2010	-	- Tighten TCR of all sizes for $10\Omega < R \leq IM\Omega$ from $\pm~200$ ppm/°C to
version /	Sep. 27, 2018		± 100 ppm/°C
			- Add SR1210, SR1218, SR2010 7W (double power)
Version 6	Oct. 02, 2017	-	- Add SR0402 7T (triple power), SR0805 47 (quadruple power),
version 6	OCt. 02, 2017		SR2512 7W (double power)
Version 5	Nov.11, 2016	-	- Update 7T power for 1206
\/i	C 01 2015		- Update SR0603 Dielectric Withstanding Voltage to 150V
Version 4	sep. 01, 2015	ep. 01, 2015 -	- Update 7T power for 0603/0805 & 7W for 1210
Version 3	Jul. 31, 2015	-	- Comply with AEC-Q200 standard
Version 2 Jan. 06, 2014		- Add SR0402/0603/1210	
	jan. 06, 2014	-	- Update electrical characteristic
Version I Mar 18, 201		I -	- Change to dual brand datasheet that describes SR0805 to SR2512 with
	Mar 18, 2011		RoHS compliant
			- Define global part number
Version 0	Oct 19, 2004	=	-



Chip Resistor Surface Mount

SERIES

SR

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

