

Light metal spirit level

ATORN®

Application

For horizontal and vertical alignment of objects



Version

- Laser-scaled horizontal round vials
- Read off 2% inclines
- Magnifying effect for improved reading
- 270° view of bubble from all positions without any interfering edges
- Made from high-strength non-breakable polycarbonate
- Strong aluminium rectangular profile
- Scratch-proof thanks to special anodising treatment
- Rubber end caps for impact protection

Advantage

- Silicone pads on rear side surface for non-slip positioning on walls
- Additional divisions for exact 0-position of bubble in the horizontal vial for precise reading (zero-point deviation in normal position: 0.5 mm/m)

Art. No.	38290 020
Length	200 mm
Measuring accuracy (per length)	0.5 mm/m

EAN-Code

4050293192056