

2N6660



SOLID STATE INC.

46 FARRAND STREET
BLOOMFIELD, NEW JERSEY 07003

www.solidstateinc.com

N-Channel Enhancement Mode
MOSPOWER


APPLICATIONS

- Switching Regulators
- Converters
- Motor Drivers

PRODUCT SUMMARY

Part Number	BV _{DSS} Volts	r _{DS(ON)} (ohms)	Package
2N6660	60	3	T0-205AD

TO-39 (TO-205AD)



BOTTOM VIEW





- 1 SOURCE
- 2 GATE
- 3 & CASE-DRAIN

ABSOLUTE MAXIMUM RATINGS (T_C = 25°C unless otherwise noted)

Parameter		2N6660	Units
V _{DS}	Drain-Source Voltage	60	V
V _{DGR}	Drain-Gate Voltage (R _{GS} = 1 MΩ)	60	V
I _D @ T _C = 25°C	Continuous Drain Current	±1.1	A
I _D @ T _C = 100°C	Continuous Drain Current	±0.8	A
I _{DM}	Pulsed Drain Current ¹	±3	A
V _{GS}	Gate-Source Voltage	±40	V
P _D @ T _C = 25°C	Max. Power Dissipation	6.25	W
P _D @ T _C = 100°C	Max. Power Dissipation	2.5	W
Junction to Case	Linear Derating Factor	0.05	W/°C
Junction to Ambient	Linear Derating Factor	0.006	W/°C
T _J	Operating and	-55 To +150	°C
T _{stg}	Storage Temperature Range		
Lead Temperature	(1/16" from case for 10 secs.)	300	°C

¹ Pulse Test: Pulswidth ≤ 300μsec, Duty Cycle ≤ 2%



ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

STATIC

Parameter	Type	Min.	Typ.	Max.	Units	Test Conditions
BV_{DSS} Drain-Source Breakdown Voltage	2N6660	60	100		V	$V_{GS} = 0$ $I_D = 10\ \mu\text{A}$
$V_{GS(th)}$ Gate-Threshold Voltage	2N6660	0.8	1.5	2	V	$V_{DS} = V_{GS}$, $I_D = 1\ \text{mA}$
I_{GSSF} Gate-Body Leakage Forward	2N6660		1 5	100 500	nA	$V_{GS} = +15\text{V}$, $V_{DS} = 0$ $V_{GS} = +15\text{V}$, $V_{DS} = 0$, $T_A = 125^\circ\text{C}$
I_{GSSR} Gate-Body Leakage Reverse	2N6660		-1	-100	nA	$V_{GS} = -15\text{V}$, $V_{DS} = 0$
I_{DSS} Zero Gate Voltage Drain Current	2N6660		1	10	μA	$V_{DS} = \text{Max. Rating}$, $V_{GS} = 0$
	2N6660		50	500	μA	$V_{DS} = 0.8\ \text{Max. Rating}$, $V_{GS} = 0$ $T_C = 125^\circ\text{C}$
$I_{D(on)}$ On-State Drain Current ¹	2N6660	1.5	1.7		A	$V_{DS} \geq 2V_{DS(ON)}$, $V_{GS} = 10\text{V}$
$V_{DS(on)}$ Static Drain-Source On-State Voltage ¹	2N6660		1.4	1.5	V	$V_{GS} = 5\text{V}$, $I_D = 0.3\text{A}$
	2N6660		2.7	3	V	$V_{GS} = 10\text{V}$, $I_D = 1\text{A}$
$R_{DS(on)}$ Static Drain-Source On-State Resistance ¹	2N6660		4.7	5	Ω	$V_{GS} = 5\text{V}$, $I_D = 0.3\text{A}$
	2N6660		2.7	3	Ω	$V_{GS} = 10\text{V}$, $I_D = 1\text{A}$
$R_{DS(on)}$ Static Drain-Source On-State Resistance ¹	2N6660		3.9	4.2	Ω	$V_{GS} = 10\text{V}$, $I_D = 1\text{A}$, $T_C = 125^\circ\text{C}$


DYNAMIC

g_{fs} Forward Transconductance ¹	2N6660	170	195		mS	$V_{DS} = 25\text{V}$, $I_D = 0.5\text{A}$
C_{iss} Input Capacitance	2N6660		35	50	pF	$V_{GS} = 0$, $V_{DS} = 25\text{V}$ $f = 1\ \text{MHz}$
C_{oss} Output Capacitance	2N6660		33	40	pF	
C_{rss} Reverse Transfer Capacitance	2N6660		2	10	pF	
t_{ON} Turn-On Time	2N6660		8	10	ns	$V_{DD} = 25\text{V}$, $I_D \cong 1\text{A}$ $R_g = 25\Omega$, $R_L = 23\Omega$ (MOSFET switching times are essentially independent of operating temperature.)
t_{OFF} Turn-Off Time	2N6660		8	10	ns	

THERMAL RESISTANCE

R_{thJC} Junction-to-Case	2N6660			20	$^\circ\text{C/W}$	
R_{thJA} Junction-to-Ambient	2N6660			170	$^\circ\text{C/W}$	Free Air Operation

BODY-DRAIN DIODE RATINGS AND CHARACTERISTICS

I_S Continuous Source Current (Body Diode)	2N6660			-1.1	A	Modified MOSPOWER symbol showing the integral P-N Junction rectifier 
I_{SM} Source Current ¹ (Body Diode)	2N6660			-3	A	$T_C = 25^\circ\text{C}$, $I_S = -1.1\text{A}$, $V_{GS} = 0$
V_{SD} Diode Forward Voltage ¹	2N6660		-0.9		V	

¹ Pulse Test: Pulse Width $\leq 300\ \mu\text{sec}$, Duty Cycle $\leq 2\%$

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

STATIC

Parameter	Type	Min.	Typ.	Max.	Units	Test Conditions
BV_{DSS} Drain-Source Breakdown Voltage	2N6660	60	100		V	$V_{GS} = 0$ $I_D = 10\ \mu\text{A}$
$V_{GS(th)}$ Gate-Threshold Voltage	2N6660	0.8	1.5	2	V	$V_{DS} = V_{GS}$, $I_D = 1\ \text{mA}$
I_{GSSF} Gate-Body Leakage Forward	2N6660		1 5	100 500	nA	$V_{GS} = +15\text{V}$, $V_{DS} = 0$ $V_{GS} = +15\text{V}$, $V_{DS} = 0$, $T_A = 125^\circ\text{C}$
I_{GSSR} Gate-Body Leakage Reverse	2N6660		-1	-100	nA	$V_{GS} = -15\text{V}$, $V_{DS} = 0$
I_{DSS} Zero Gate Voltage Drain Current	2N6660		1	10	μA	$V_{DS} = \text{Max. Rating}$, $V_{GS} = 0$
	2N6660		50	500	μA	$V_{DS} = 0.8\ \text{Max. Rating}$, $V_{GS} = 0$ $T_C = 125^\circ\text{C}$
$I_{D(on)}$ On-State Drain Current ¹	2N6660	1.5	1.7		A	$V_{DS} \geq 2V_{DS(ON)}$, $V_{GS} = 10\text{V}$
$V_{DS(on)}$ Static Drain-Source On-State Voltage ¹	2N6660		1.4	1.5	V	$V_{GS} = 5\text{V}$, $I_D = 0.3\text{A}$
	2N6660		2.7	3	V	$V_{GS} = 10\text{V}$, $I_D = 1\text{A}$
$R_{DS(on)}$ Static Drain-Source On-State Resistance ¹	2N6660		4.7	5	Ω	$V_{GS} = 5\text{V}$, $I_D = 0.3\text{A}$
	2N6660		2.7	3	Ω	$V_{GS} = 10\text{V}$, $I_D = 1\text{A}$
$R_{DS(on)}$ Static Drain-Source On-State Resistance ¹	2N6660		3.9	4.2	Ω	$V_{GS} = 10\text{V}$, $I_D = 1\text{A}$, $T_C = 125^\circ\text{C}$


DYNAMIC

g_{fs} Forward Transconductance ¹	2N6660	170	195		mS	$V_{DS} = 25\text{V}$, $I_D = 0.5\text{A}$
C_{iss} Input Capacitance	2N6660		35	50	pF	$V_{GS} = 0$, $V_{DS} = 25\text{V}$ $f = 1\ \text{MHz}$
C_{oss} Output Capacitance	2N6660		33	40	pF	
C_{rss} Reverse Transfer Capacitance	2N6660		2	10	pF	
t_{ON} Turn-On Time	2N6660		8	10	ns	$V_{DD} = 25\text{V}$, $I_D \cong 1\text{A}$ $R_g = 25\ \Omega$, $R_L = 23\ \Omega$ (MOSFET switching times are essentially independent of operating temperature.)
t_{OFF} Turn-Off Time	2N6660		8	10	ns	

THERMAL RESISTANCE

R_{thJC} Junction-to-Case	2N6660			20	$^\circ\text{C/W}$	
R_{thJA} Junction-to-Ambient	2N6660			170	$^\circ\text{C/W}$	Free Air Operation

BODY-DRAIN DIODE RATINGS AND CHARACTERISTICS

I_S Continuous Source Current (Body Diode)	2N6660			-1.1	A	Modified MOSPOWER symbol showing the integral P-N Junction rectifier 
I_{SM} Source Current ¹ (Body Diode)	2N6660			-3	A	
V_{SD} Diode Forward Voltage ¹	2N6660		-0.9		V	$T_C = 25^\circ\text{C}$, $I_S = -1.1\text{A}$, $V_{GS} = 0$

¹ Pulse Test: Pulse Width $\leq 300\ \mu\text{s}$, Duty Cycle $\leq 2\%$

TYPICAL PERFORMANCE CURVES (25° C unless otherwise noted)

FIGURE 1. Ohmic Region




FIGURE 2. Transfer Characteristics




FIGURE 3. Temperature Effects on $r_{DS(on)}$




FIGURE 4. Threshold Region





FIGURE 5. Off-State Current



TYPICAL PERFORMANCE CURVES (25°C unless otherwise noted)

FIGURE 1. Ohmic Region




FIGURE 2. Transfer Characteristics




FIGURE 3. Temperature Effects on $r_{DS(on)}$




FIGURE 4. Threshold Region





FIGURE 5. Off-State Current



TRANSIENT THERMAL RESPONSE CURVES






FIGURE 1. TO-39 Package

TO-39 (TO-205AD)



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	6.10	6.60	0.240	0.260
A ₁	0.23	1.04	0.009	0.041
Øb	0.41	0.53	0.016	0.021
ØD	8.51	9.39	0.335	0.370
ØD ₁	7.75	8.51	0.305	0.335
e	5.08 BSC		0.200 BSC	
e ₁	2.54 BSC		0.100 BSC	
j	0.72	0.86	0.028	0.034
k	0.74	1.14	0.029	0.045
L	12.70	19.05	0.500	0.750