

3-sided shelf trolley with 4 load areas, load capacity 600 kg

Height 1800 mm, 3 load area sizes

fetra
Transportgeräte

Application:

For transporting non-stacking goods and materials, for permanent use in industrial applications.

Execution:

- Module system, can be completely fixed with screws
- Steel tube/profile steel welded
- Front walls with vertical tube struts (distance approx. 130 mm)
- 1 firm and 3 loose shelving levels
- variable screw-in to the grid of 100 mm
- Rigid sandwich plates

Advantage:

- Robust design and high load capacity ensure a long service life even when used for high industrial loads
- Multiple load areas provide ample storage space for non-stacking goods and crates
- FETRA plug-and-screw design allows trolleys and accessories to be altered easily
- Large high-quality rollers for good running properties
- Vertical tubular struts prevent parts from falling down

Delivery:

Flat-packed



Art. no.	50268 686
Brand	FETRA
Manufacturer Part Number	8312-1
Material of loading surface	Wood
Load-carrying capacity	600 kg
Load-carrying capacity of loading surfaces	90 kg
Grid dimension of upper ends	100 mm
Number of loading surfaces	4 PCS
Loading surface size	1000 x 700 mm
Loading-surface width	700 mm
Loading-surface height	269 mm, 669 mm, 1069 mm, 1469 mm
Loading surface length	1000 mm
Height	1800 mm
Number of panels	3 PCS
Material of wall	Strut brace
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
With wheel lock	Yes
Total stop optional	Yes
Wheel width	40 mm
Wheel diameter	200 mm
Material of wheel	TPE
Colour	Brilliant blue RAL 5007
Surface	Powder-coated
EN standard	1757-3
Design	With strut braces on three sides
Gross Weight	98.000 kg
Product Group	5AB

EAN

4017976831213