

SDJC clamp holder positive, left-hand

For longitudinal and copy turning with DC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with DC indexable insert 55°

Version

- Precision-made steel carrier, burnished, hardened, type D, attack angle 93°, tip angle 55°, clearance angle 7°

Advantage

- Narrow geometry optimised for contour-turning work
- Positive body geometry ensures low cutting forces
- Very good surfaces, for medium and finishing infeed



Art. no.	17831 067
ISO name	SDJC R/L 2020 K11
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	20.5 mm
Programming size	25 mm
Suitable for indexable inserts	DC.. 11T3..
Tool design	Left
DIN	4983

EAN-Code

4050293566406