

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: SPL

Supplier's address: Schiefer Lighting, Potterbakkerstraat 35, 4871EP Etten-Leur, NL

Model identifier: L642745827

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	GU10		
Mains or non-mains:	MLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Only with specific dimmers

Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------

General product parameters:

Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	8	Energy efficiency class	F
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	450 in Narrow cone (90°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2 700
On-mode power (P_{on}), expressed in W	7,5	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	82
Outer dimensions without separate control gear, light-	Height	54	Spectral power distribution in the range 250 nm to 800 nm, at full-load
	Width	50	
	Depth	50	
			See image in last page

ing control parts and non-lighting control parts, if any (millimetre)			
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,461 0,417
Parameters for directional light sources:			
Peak luminous intensity (cd)	700	Beam angle in degrees, or the range of beam angles that can be set	36
Parameters for LED and OLED light sources:			
R9 colour rendering index value	-3	Survival factor	0,70
the lumen maintenance factor	0,70		
Parameters for LED and OLED mains light sources:			
displacement factor (cos ϕ_1)	0,70	Colour consistency in McAdam ellipses	5
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	.. ^(b)	If yes then replacement claim (W)	-
Flicker metric (Pst LM)	0,7	Stroboscopic effect metric (SVM)	0,9

(a)'.-' : not applicable;

(b)'.-' : not applicable;


SPL Spectrum Test Report

Sample	:		Date	:	2021-07-22 09:50:59
Specification	:	L642745827	Sam. Status	:	
Sample No.	:	2	Instrument	:	HaasSuite(EVERFINE)
Manufacturer	:	Renee	Test by	:	Renee
			Assessor	:	damin

Test Condition

Temperature	:	25.3Deg	RH	:	65.0%
WL Range	:	380nm-780nm	IP	:	47136 (72%)
Test Mode	:	Fast Test	T	:	35 ms
			Sensitivity	:	High

Spectrum



Colorimetric Parameters

Chromaticity Coordinate: $x = 0.4605$ $y = 0.4172$ / $u' = 0.2600$ $v' = 0.5299$ ($duv=2.35e-03$)
 CCT= 2741K Prcp WL: Ld=583.3nm Purity=63.5%
 Peak WL: Lp=604nm FWHM: =110.3nm Ratio:R=24.4% G=73.2% B=2.4%

Render Index: Ra = 80.4

R1 =79 R2 =91 R3 =94 R4 =77 R5 =79 R6 =91 R7 =80
 R8 =53 R9 =-3 R10=81 R11=77 R12=75 R13=82 R14=97 R15=69
 LEVEL:OUT WHITE:ANSI_2700K

Photometric & Radiometric Parameters

Flux = 574.85 lm Eff. : 134.31 lm/W Fe = 1.7242 W

Electrical parameters

V = 229.9 V I = 0.02047 A P = 4.260 W PF = 0.9094