DATASHEET - LS-11S/RL



$Position\ switches,\ 1N/O+1N/C,\ rotary\ lever,\ snap-action\ contact$

Powering Business Worldwide*

Part no. LS-11S/RL Catalog No. 266117 Eaton Catalog No. LS-11S/RL EL-Nummer 4356126

(Norway)

Delivery program

Delivery program		
Basic function		Position switches Safety position switches
Part group reference		LS(M)
Product range		Rotary lever
Degree of Protection		IP66, IP67
Features		Complete unit
Ambient temperature	°C	-25 - +70
Design		EN 50047 Form A
Snap-action contact		Yes
Contacts		
N/O = Normally open		1 N/0
N/C = Normally closed		1 NC →
Notes		e safety function, by positive opening to IEC/EN 60947-5-1
Contact sequence		0-\frac{13}{14}\frac{1}{22}
Contact travel = Contact closed = Contact open		21-20 21-3-14 21-22 13-14 15' 2W = 60'
Positive opening (ZW)		yes
Colour		
Enclosure covers		Yellow
Enclosure covers		
Housing		Insulated material
Connection type		Cage Clamp
Notes		Cage-Clamp is a registered trademark of Wago Kontakttechnik, 32432 Minden, Germany. Accessories for the Cage-Clamp terminals from Wago:power comb, gray, Wago Article No. 264-402
Notes The operating head can be rotated at 90° intervals to adapt to the specified a	pproach direction.	

Technical data

General

General		
Standards		IEC/EN 60947
Climatic proofing		Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Ambient temperature	°C	-25 - +70

Mounting position As required Degree of Protection 1P66, 1P67 Terminal capacities mm² 1 x (0.5 - 2.5) Solid mm² 1 x (0.5 - 1.5) Flexible with ferrule mm² 1 x (0.5 - 1.5) Contacts/switching capacity Rated impulse withstand voltage U _{imp} V AC 4000 Rated insulation voltage U _i V 400 Rated operational current I ₀ A 4 AC-15 U _i A 6 220 V 230 V 240 V I ₀ A 6 220 V 230 V 240 V I ₀ A 4 DC-13 U _i A 4 24 V I ₀ A 4 DC-13 U _i A 0.6 220 V I ₀ A 0.6 220 V I ₀ A 0.6 110 V I ₀ A 0.6 220 V I ₀ A 0.6 Control circuit reliabilit
Terminal capacities
Solid
Flexible with ferrule
Contacts/switching capacity Name VAC 4000 Rated impulse withstand voltage Ui V 4000 Rated insulation voltage Ui V 400 Overvoltage category/pollution degree III/3 III/3 Rated operational current Ie A 6 AC-15 Separational current Ie A 6 24 V Ie A 6 6 380 V 400 V 415 V Ie A 4 4 DC-13 Ie A 3 3 Image: Control circuit reliability Ie A 0.5 Image: Control circuit reliability Ie A 0.5 Image: Control circuit reliability Image: Control ci
Rated impulse withstand voltage U _{imp} V AC 4000 Rated insulation voltage U _i V 400 Overvoltage category/pollution degree III/3 IIII/3 Rated operational current Ie A
Nation N
Networksage category/pollution degree III/3
Rated operational current
AC-15 24 V 1e A 6 220 V 230 V 240 V 1e A 6 380 V 400 V 415 V 1e A 4 DC-13 24 V 1e A 3 110 V 1e A 0.6 220 V 220 V 1e A 0.3 Control circuit reliability #F Fault probability 41 24 V DC/5 mA 45 Fault probability Fault probability 10 -7, < 1 fault in 107 operations Fault probability 10 -6, < 1 failure at 5 x 10 ⁶ operations Supply frequency Short-circuit rating to IEC/EN 60947-5-1
Part Pault
220 V 230 V 240 V
380 V 400 V 415 V Ie
DC-13 24 V Ie A 3 110 V Ie A 0.6 220 V Ie A 0.3 Control circuit reliability at 24 V DC/5 mA HF Fault probability The standard of the
DC-13 24 V Ie A 3 110 V Ie A 0.6 220 V Ie A 0.3 Control circuit reliability at 24 V DC/5 mA HF Fault robability The probability Fault robability The probability Supply frequency Hz Max. 400 Max. 400
110 V Ie A 0.6 220 V Ie A 0.3 Control circuit reliability at 24 V DC/5 mA HF Fault probability HF Fault probability Fault probability The state of the s
110 V I _e A 0.6 220 V I _e A 0.3 Control circuit reliability at 24 V DC/5 mA HF Fault probability at 5 V DC/1 mA HF Fault probability Supply frequency Hz max. 400
220 V Le A 0.3 Control circuit reliability at 24 V DC/5 mA HF Fault probability A 10 -7, < 1 fault in 107 operations probability The substitution of the substit
Control circuit reliability at 24 V DC/5 mA H _F Fault v 10 ⁻⁷ , < 1 fault in 107 operations probability At 5 V DC/1 mA H _F Fault v 10 ⁻⁶ , < 1 failure at 5 x 10 ⁶ operations probability Supply frequency Hz max. 400
at 24 V DC/5 mA HF Fault probability 10 -7, < 1 fault in 107 operations at 5 V DC/1 mA HF Fault probability 40 -6, < 1 failure at 5 x 10 operations Bupply frequency Hz max. 400
at 5 V DC/1 mA H _F Fault probability Supply frequency Hz max. 400 Short-circuit rating to IEC/EN 60947-5-1
Supply frequency Hz max. 400 Short-circuit rating to IEC/EN 60947-5-1
Short-circuit rating to IEC/EN 60947-5-1
max. fuse A gG/gL 6
Repetition accuracy mm 0.15
Mechanical variables
Lifespan, mechanical Operations x 10 ⁶ 8
Mechanical shock resistance (half-sinusoidal shock, 20 ms)
Standard-action contact g 25
Operating frequency Operations/h ≤ 6000
Actuation
Mechanical
Actuating force at beginning/end of stroke N 1.0/8.0
Actuating torque of rotary drives Nm 0.2
Max. operating speed with DIN cam m/s 1.5
Notes $\qquad \qquad \text{for angle of actuation } \alpha = 0^{\circ}$

Design verification as per IEC/EN 61439

In	Α	6
P_{vid}	W	0.17
P_{vid}	W	0
P_{vs}	W	0
P _{diss}	W	0
	°C	-25
	°C	70
		Meets the product standard's requirements.
		Meets the product standard's requirements.
		Meets the product standard's requirements.
		Meets the product standard's requirements.
	P _{vid} P _{vid} P _{vs}	P _{vid} W P _{vid} W P _{vs} W P _{diss} W °C

10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0

Sensors (EG000026) / End switch (EC000030)

Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Position switch (Type 1)


(ecl@ss10.0.1-27-27-06-01 [AGZ382015])		
Width sensor	mm	31
Diameter sensor	mm	0
Height of sensor	mm	61
Length of sensor	mm	33.5
Rated operation current le at AC-15, 24 V	Α	6
Rated operation current le at AC-15, 125 V	Α	6
Rated operation current le at AC-15, 230 V	Α	6
Rated operation current le at DC-13, 24 V	Α	3
Rated operation current le at DC-13, 125 V	Α	0.8
Rated operation current le at DC-13, 230 V	Α	0.3
Switching function		Quick-break switch
Switching function latching		No
Output electronic		No
Forced opening		Yes
Number of safety auxiliary contacts		1
Number of contacts as normally closed contact		1
Number of contacts as normally open contact		1
Number of contacts as change-over contact		0
Type of interface		None
Type of interface for safety communication		None
Construction type housing		Cuboid
Material housing		Plastic
Coating housing		Other
Type of control element		Rotary lever
Alignment of the control element		Other
Type of electric connection		Other
With status indication		No
Suitable for safety functions		Yes
Explosion safety category for gas		None
Explosion safety category for dust		None

Ambient temperature during operating	°C	25 - 70
Degree of protection (IP)		IP67
Degree of protection (NEMA)		4X


Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	IEC: IP66, 67, UL/CSA Type 3R, 4X (indoor use only), 12, 13

Dimensions



- ① Tightening torque of cover screws: 0.8 Nm \pm 0.2 Nm ② only with LS (insulated version) ③ Fixing screws 2 x M4 \geq 30 M_A = 1.5 Nm



Additional product information (links)

IL053001ZU LS-Titan position switch: basic device