


Multilayer Capacitors, SMD



Capacitor



SPECIFICATION:

Ceramic type	NPO
Temperature range	-55...+125 °C

PRODUCT RANGE:

Art. Nr.	Capacitance	Rated voltage	Construction form	Capacitance tolerance	Dimensions L x H x W	Height	Length	Width
	1.5 pF	200 VDC	1206	±0.25 pF	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	1.5 pF	630 VDC	1206	±0.25 pF	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	3.3 pF	1000 VDC	1206	±0.25 pF	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	4.7 pF	1000 VDC	1206	±0.25 pF	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	4.7 pF	2000 VDC	1206	±0.25 pF	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	6.8 pF	1000 VDC	1206	±0.25 pF	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	10 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	10 pF	2000 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	15 pF	200 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	15 pF	630 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	22 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	22 pF	100 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	22 pF	200 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	22 pF	630 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	22 pF	1000 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	22 pF	2000 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	33 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	33 pF	100 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	33 pF	200 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	33 pF	630 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	33 pF	1000 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	33 pF	2000 VDC	1206	±5%	3.2 x 0.95 x 1.6 mm	0.95 mm	3.2 mm	1.6 mm
	47 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	47 pF	1000 VDC	1206	±5%	3.2 x 0.95 x 1.6 mm	0.95 mm	3.2 mm	1.6 mm
	47 pF	1000 VDC	1206	±10%	3.2 x 0.95 x 1.6 mm	0.95 mm	3.2 mm	1.6 mm
	68 pF	200 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	68 pF	1000 VDC	1206	±5%	3.2 x 0.95 x 1.6 mm	0.95 mm	3.2 mm	1.6 mm
	68 pF	2000 VDC	1206	±5%	3.2 x 1.25 x 1.6 mm	1.25 mm	3.2 mm	1.6 mm
	100 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	100 pF	100 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	100 pF	500 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	100 pF	630 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	100 pF	2000 VDC	1206	±5%	3.2 x 0.95 x 1.6 mm	0.95 mm	3.2 mm	1.6 mm
	150 pF	1000 VDC	1206	±5%	3.2 x 1.6 x 1.6 mm	1.6 mm	3.2 mm	1.6 mm

Art. Nr.	Capacitance	Rated voltage	Construction form	Capacitance tolerance	Dimensions L x H x W	Height	Length	Width
	220 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	220 pF	100 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	220 pF	200 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	220 pF	630 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	220 pF	2000 VDC	1206	±5%	3.2 x 1.6 x 1.6 mm	1.6 mm	3.2 mm	1.6 mm
	330 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	330 pF	100 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	470 pF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	470 pF	100 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	470 pF	500 VDC	1206	±5%	3.2 x 0.95 x 1.6 mm	0.95 mm	3.2 mm	1.6 mm
	470 pF	1000 VDC	1206	±5%	3.2 x 1.6 x 1.6 mm	1.6 mm	3.2 mm	1.6 mm
	1 nF	100 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm
	1 nF	200 VDC	1206	±5%	3.2 x 1.6 x 1.6 mm	1.6 mm	3.2 mm	1.6 mm
	1 nF	630 VDC	1206	±5%	3.2 x 1.6 x 1.6 mm	1.6 mm	3.2 mm	1.6 mm
	2.2 nF	200 VDC	1206	±5%	3.2 x 1.25 x 1.6 mm	1.25 mm	3.2 mm	1.6 mm
	3.3 nF	50 VDC	1206	±5%	3.2 x 0.8 x 1.6 mm	0.8 mm	3.2 mm	1.6 mm