


# SU8000

## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF



installation length with pipe adapter E40152 / E40155: 205 mm  
installation length with pipe adapter E40153 / E40156: 215 mm



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	0...100 l/min	0...6 m³/h
Process connection	threaded connection G 1 flat seal	

### Application

Special feature	Gold-plated contacts
Application	totaliser function; for industrial applications
Installation	connection to pipe by means of an adapter
Media	water; glycol solutions; coolants; oil
Note on media	low-viscosity oils with viscosity: 7...40 mm²/s (40 °C) high-viscosity oils with viscosity: 30...68 mm²/s (40 °C)
Medium temperature [°C]	-10...80
Pressure rating [bar]	16

### Electrical data

Operating voltage [V]	19...30 DC; (according to EN 50178 SELV/PELV)
Current consumption [mA]	100
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	10

### Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

# SU8000



## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF

Inputs		
Inputs		counter reset
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; pulse signal; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250; (per output)
Number of analogue outputs		1
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Analogue voltage output	[V]	0...10; (scalable)
Min. load resistance	[Ω]	2000
Pulse output		flow rate meter
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range		0...100 l/min
Display range		0...120 l/min
Resolution		0.1 l/min
Set point SP		0.2...100 l/min
Reset point rP		0...99.8 l/min
Analogue start point ASP		0...80 l/min
Analogue end point AEP		20...100 l/min
Max. flow rate		110 l/min
In steps of		0.1 l/min
Volumetric flow quantity monitoring		
Pulse value		0.1 l...1 000 000 m³
Pulse length	[s]	0,025...2
Temperature monitoring		
Measuring range	[°C]	-10...80
Resolution	[°C]	0.2
Set point SP	[°C]	-9.8...80
Reset point rP	[°C]	-10...79.8
Analogue start point	[°C]	-10...62
Analogue end point	[°C]	8...80
In steps of	[°C]	0.2

# SU8000



## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF

Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		< ± (3 % MW + 0,2 % MEW) / < ± (5 % MW + 0,5 % MEW); (water; glycol: 35%; oil: viscosity 68 mm <sup>2</sup> /s at 40 °C)
Repeatability		0,2 l/min; 12 l/h; 0,012 m <sup>3</sup> /h
Temperature monitoring		
Accuracy	[K]	± 3 (Q > 1 l/min)
Response times		
Flow monitoring		
Response time	[s]	0.25; (dAP = 0)
Delay time programmable dS, dr	[s]	0...50
Damping for the switching output dAP	[s]	0...1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 70 (Q > 5 l/min); (water)
Software / programming		
Parameter setting options		Flow monitoring; quantity meter; Preset counter; Temperature monitoring
Operating conditions		
Ambient temperature	[°C]	-10...60
Storage temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
MTTF [years]		185
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight	[g]	1711
Materials		housing: AlMgSi0,5 anodised; Sealing: FKM; connector housing: brass Optalloy-plated; PA 6.6; cover film: PA
Materials (wetted parts)		stainless steel (1.4404 / 316L); FKM; PES; Centellen 200
Process connection		threaded connection G 1 flat seal
Displays / operating elements		
Display	Display unit	6 x LED, green (l/min, m <sup>3</sup> /h, l, m <sup>3</sup> , 10 <sup>3</sup> , °C)
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit

# SU8000



## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF

### Accessories

Accessories (supplied)

sealings: 2, Centellen

adapter for pipe: 1 x R1/2, stainless steel, E40179

adapter for pipe: 1 x R3/4, stainless steel, E40180

adapter for pipe: 1 x R1/2, brass, E40152

adapter for pipe: 1 x R3/4, brass, E40153

### Remarks

MW = measured value

Remarks

MEW = Final value of the measuring range

sealing: only with supplied Centellen seals

Pack quantity


1 pcs.

### Electrical connection

Connector: 1 x M12; Moulded body: brass, Optalloy-plated; Contacts: gold-plated



### Connection



OUT1: switching output volumetric flow quantity monitoring

Pulse output quantity meter

signal output Preset counter

OUT2/InD: switching output volumetric flow quantity monitoring / Temperature monitoring

analogue output volumetric flow quantity monitoring / Temperature monitoring

input counter reset

# SU8000


## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF



### Diagrams and graphs

#### Pressure loss



$dP$  Pressure loss

$Q$  volumetric flow quantity