

Miniature cutting insert, type AG HW56 15

For internal recessing

ATORN[®]



Application

For internal recessing in the material groups steel and (stainless steel) at low to high cutting speeds and under average cutting conditions.

Version

- Solid carbide cutting insert with internal cooling

Advantage

- Very hard cemented carbide grade ensures low wear
- Stable geometry for the cutting insert
- Extremely sharp blades ensure process reliability for cutting

Art. no.	17129 646
ISO name	AG
Shaft diameter	6 mm
Length	51 mm
Clearance length	15 mm
Programming size 2	1.4 mm
Recessing width	1 mm
Programming size	2.8 mm
Min. bore diameter	6.1 mm
Machining direction	Left
Carbide type	HW56 15
Material to be processed	Stainless steel, Non-ferrous metal

EAN-Code

4050293378399