

PTFN steel boring bar, negative, right

for longitudinal turning using TN indexable insert

ATORN[®]

Application


For longitudinal turning using TN 60° indexable insert

Version

- precision-manufactured steel boring bar, T type, 90° pitch angle, 60° tip angle, 0° clearance angle

Advantage

- three-edge geometry lowers costs per cut
- negative body geometry ensures good stability and absorption of force for large cutting depths



Art. No.	17858 151
ISO name	A 32 S PTFN R/L 16
Min. bore diameter	40 mm
Shaft diameter	32 mm
Clearance length	50 mm
Length	250 mm
Clamping surface height	15 mm
Programming size	22 mm
Cutting edge height	15 mm
Suitable for indexable inserts	TN.. 1604..
Tool design	Right

EAN-Code

4050293348439