

Short taper-flange

Made of cast iron



Application:

For retroactive fastening of lathe chucks.

Execution:

- Ready-machined on machine side and chuck side, spindle heads with camlock fastening in accordance with DIN ISO 702-2 (formerly DIN 55029).

Art. no.	22510 105
Brand	BISON
Manufacturer Part Number	358245242300
Flange diameter	200 mm
Taper shank size	5
Pitch circle diameter	176 mm
Taper diameter	82.575 mm
Drill hole	79.5 mm
Ratio	160 mm
Number of bolts	6/4 pieces
Flange thickness	30 mm
Thread dimension	M10 x 6
Gross Weight	5.211 kg
Product Group	221

