

























Heatsinks for transistors in plastic case

| | | |
|--|---|--|
| <p>art. no.</p> <p>FK 209 SA 32</p> |  |  <p>25 K/W  SOT 32</p>  |
| <p>available without hole pattern as well</p> | | |
| <p>art. no.</p> <p>FK 210 SA CB</p> |  |  <p>18 K/W  CB (SOT 32 + TO 220)</p>  |
| <p>available without hole pattern as well</p> | | |
| <p>art. no.</p> <p>FK 213 SA 32</p> |  |  <p>21 K/W  SOT 32</p>  |
| <p>available without hole pattern as well</p> | | |
| <p>art. no.</p> <p>FK 214 SA CB</p> |  |  <p>15 K/W  CB (SOT 32 + TO 220)</p>  |
| <p>available without hole pattern as well</p> | | |
| <p>art. no.</p> <p>FK 231 SA 220</p> |  |  <p>24 K/W  TO 220</p>  |
| <p>art. no.</p> <p>FK 239 SA 32</p> |  |  <p>24 K/W  SOT 32</p>  |
| <p>material:</p> <p>surface:</p> | <p>aluminium</p> <p>black anodised</p> | |