

## FEATURES

- **Black Neoprene Rubber**
- **Flexible**
- **Durable**
- **Customisable**
- **Resistant to ozone, sunlight and atmospheric ageing**

## RS PRO Black Rubber Sheet, 1m x 2m x 1.5mm

RS Stock No.: 733-6753



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Introducing a series of neoprene rubber sponge sheets from RS PRO. These black neoprene rubber sheets are suitable for use, both indoor & outdoor, offer moderate resistance to atmospheric ageing, sunlight, oils, and greases.

### RS PRO Rubber Sheet Options

- 1 m x 2 m x 1.5mm - RS Stock no: 733-6753
- 1 m x 2 m x 1.5mm - RS Stock no: 733-6731
- 1 m x 2 m x 3mm - RS Stock no: 733-6757
- 1 m x 2 m x 16mm – RS Stock no: 733-6741
- 1 m x 2 m x 3mm - RS Stock no: 733-6735
- 1 m x 2 m x 6mm - RS Stock no: 733-6744
- 1 m x 2 m x 6mm - RS Stock no: 733-6766
- 1 m x 2 m x 10mm - RS Stock no: 733-6747
- 1 m x 2 m x 10mm - RS Stock no: 733-6769
- 1 m x 2 m x 20mm - RS Stock no: 733-6750
- 1 m x 2 m x 25mm - RS Stock no: 103-4059

## General Specifications

<b>Colour</b>	Black
<b>Density</b>	122kg/m <sup>3</sup>
<b>Adhesive Backing</b>	Yes
<b>Suitability</b>	Animal Oil, Cold Water, Dilute Acid, Dilute Alkali, Ethylene Glycol, Fuel, Hot Water, Vegetable Oil
<b>Elongation</b>	>180%
<b>Water Absorption</b>	0.8
<b>Compression Set (50% 22h 20°C)</b>	19.10%
<b>Resistance to Air+UV</b>	Excellent
<b>Resistance to Oil</b>	Poor
<b>Resistance to Acids</b>	Good
<b>Environmental Protection</b>	CFC and HFC FREE / CAN BE RECYCLED
<b>Application</b>	Sound-proofing, Noise and Heat insulation

## Mechanical Specifications

<b>Length</b>	1m
<b>Thickness</b>	10mm
<b>Width</b>	2m
<b>Tensile Strength</b>	>500KN/m <sup>2</sup>

## Operation Environment Specifications

<b>Maximum Operating Temperature</b>	85°C
<b>Minimum Operating Temperature</b>	-40°C

## Approvals

<b>Flammability Rating</b>	UL 94 HF-1
----------------------------	------------