

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 31_BNC-50-0-1/133_N

Rev.: A 

Description

Adaptor jack/jack

Interface standards
IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
Frequency range	DC to 4 GHz
Return loss	≥ dB

Mechanical Data

Weight	0.0123 kg
--------	-----------

Environmental Data

Operating Temperature 2002/95/EC (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DCA-00013802
-------------------	--------------

Ordering Information

Single package	31_BNC-50-0-1/133_NE
Bulk 100 pcs package	31_BNC-50-0-1/133_NH

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions