


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
	<b>SKINTOP® MSR-M ATEX</b>	07.11.2014

For the benefits, refer to SKINTOP® MS-M ATEX



Good chemical resistance



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

### Application range

With reducing seal insert, to seal cables with smaller outer diameters.

### Product Make-up

Metric connection thread acc. to EN 50262


### Note

Refer to SKINTOP® SDVR-M ATEX for suitable accessories

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: LAPP_PRO994EN.pdf	1 / 4
--------------------	-----------------------------	-------


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
	<b>SKINTOP® MSR-M ATEX</b>	<b>07.11.2014</b>


### Technical Data

Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEX IBE 13.0026X
Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: cable screw gland
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-30°C to +90°C

Product Management	Document: LAPP_PRO994EN.pdf	2 / 4
--------------------	-----------------------------	-------

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINTOP® MSR-M ATEX						
53112705	12 x 1,5	2 - 5	16	26,5	6.5	100
53112715	16 x 1,5	4 - 7	20	33.0	7.0	100
53112725	20 x 1,5	5 - 10	24	37.0	8.0	50
53112735	25 x 1,5	6 - 13	29	38,5	8.0	25
53112745	32 x 1,5	7 - 15	36	45,5	9.0	25
53112755	40 x 1,5	16 - 23	45	48.0	9.0	10
53112765	50 x 1,5	19 - 29	54	55,5	10.0	5
53112775	63 x 1,5	32 - 39	67	67.0	15.0	5

U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	 <b>LAPP GROUP</b>
	<b>SKINTOP® MSR-M ATEX</b>	07.11.2014



Product Management	Document: LAPP_PRO994EN.pdf	4 / 4
--------------------	-----------------------------	-------