



SIMATIC DP, ELECTRONIC MODULE FOR ET 200S, 4 AI TC, +/- 80MV; 15 MM WIDE, 15 BIT + SIGN WITH LED SF (GROUP FAULT).

Supply voltage

Load voltage L+

- Rated value (DC) 24 V; From power module
- Reverse polarity protection Yes

Input current

from load voltage L+ (without load), max.	30 mA
from backplane bus 3.3 V DC, max.	10 mA

Power losses

Power loss, typ.	0.6 W
------------------	-------

Address area

Address space per module

- Address space per module, max. 8 byte

Analog inputs

Number of analog inputs	4
permissible input voltage for voltage input (destruction limit), max.	10 V; Permanent
Cycle time (all channels) max.	Number of active channels per module x basic conversion time
Technical unit for temperature measurement adjustable	No

Input ranges

- Voltage Yes
- Current No
- Thermocouple Yes
- Resistance thermometer No

• Resistance	No
Input ranges (rated values), voltages	
• -80 mV to +80 mV	Yes
• Input resistance (-80 mV to +80 mV)	1 MΩ
Input ranges (rated values), thermoelements	
• Type B	Yes
• Input resistance (Type B)	1 MΩ
• Type E	Yes
• Input resistance (Type E)	1 MΩ
• Type J	Yes
• Input resistance (type J)	1 MΩ
• Type K	Yes
• Input resistance (Type K)	1 MΩ
• Type L	Yes
• Input resistance (Type L)	1 MΩ
• Type N	Yes
• Input resistance (Type N)	1 MΩ
• Type R	Yes
• Input resistance (Type R)	1 MΩ
• Type S	Yes
• Input resistance (Type S)	1 MΩ
• Type T	Yes
• Input resistance (Type T)	1 MΩ
Thermocouple (TC)	
Temperature compensation	
— internal temperature compensation	Not possible
— external temperature compensation with compensations socket	Yes; possible, one external compensating box per channel
Characteristic linearization	
• Parameterizable	Yes; Type B, E, J, K, L, N, R, S, T to IEC 584
Cable length	
• shielded, max.	50 m
Analog value creation	
Measurement principle	integrating
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit; 15 bits + sign
• Integration time, parameterizable	Yes
• Integration time (ms)	16,7 / 20 ms
• Conversion time (per channel)	65 ms; 55 / 65 ms (additional 20 ms on activated wire-break test)
Smoothing of measured values	

• Parameterizable	Yes; In four stages by means of digital filtering
• Step: None	Yes; 1 x cycle time
• Step: low	Yes; 4 x cycle time
• Step: Medium	Yes; 32 x cycle time
• Step: High	Yes; 64 x cycle time

Encoder

Connection of signal encoders	
• for voltage measurement	Yes

Errors/accuracies

Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to input area), (+/-)	0.05 %
Operational limit in overall temperature range	
• Voltage, relative to input area, (+/-)	0.6 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to input area, (+/-)	0.4 %
Interference voltage suppression for $f = n \times (f_1 +/ - 1\%)$, f_1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	70 dB
• common mode voltage (USS < 2.5 V) , min.	90 dB

Isochronous mode

Isochronous operation (application synchronized up to terminal)	No
Diagnostic messages	
• Diagnostic functions	Yes; Can be read out
• Diagnostic information readable	Yes
• Wire break	Yes; A break in the wire is only detected for thermocouples
• Group error	Yes
• Overflow/underflow	Yes
Diagnostics indication LED	
• Group error SF (red)	Yes

Parameter

Remark	4 byte
Diagnosis: wire break	Disable / enable (wire break is detected only in thermocouples)
Measurement type/range	Deactivated/ +/- 80 mV/ TC-EL Type T (Cu-CuNi)/ TC-EL Type K (NiCr-Ni)/ TC-EL Type B (PtRh-PtRh)/ TC-EL Type c (Wer-Wer) TC-EL Type N (NiCrSi-NiSi)/ TC-EL Type E (NiCr-CuNi)/ TC-EL Type R (PtRh-Pt)/ TC-EL Type S (PtRh-Pt)/ TC-EL Type J (Fe-Cu-Ni)/ TC
Group diagnostics	Disable / enable

Overflow/underflow	Disable / enable
Comparison point	none / RTD
Comparison point number	None / 1 / 2 / 3 / 4 / 5 / 6 / 7 / 8
Unit	Celsius

Galvanic isolation

Galvanic isolation analog inputs	
• between the channels	No
• between the channels and the backplane bus	Yes
• between the channels and the load voltage L+	Yes

Permissible potential difference

between inputs and MANA (UCM)	2 V AC PP
between MANA and M internally (UISO)	75V DC/60V AC

Isolation

Isolation checked with	500 V DC
------------------------	----------

Dimensions

Width	15 mm
Height	81 mm
Depth	52 mm

Weights

Weight, approx.	40 g
-----------------	------

last modified:

12.03.2015