Axial Lead Fuse, 6.3x32 mm, low resistance, up to 30 A





UL 248-14 · 250 V · Time-Lag T

See below:

Approvals and Compliances

Description

- Up to 30 A, low resistance
- Ceramic Tube

Applications

- Single-phase high current applications up to 30 A

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Detailed request for product

Technical Data	
Rated Voltage	250 V
Rated current	12 - 30 A
Breaking Capacity	500 A
Characteristic	Time-Lag T
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/21 acc. to IEC 60068-1
Material: Tube	Ceramics
Material: Endcaps	Nickel-Plated Brass
Material: Axial Leads	Tin-Plated Copper
Material: Filler	Sand
Unit Weight	3.9 g
Storage Conditions	0°C to 60°C, max. 70% r.h.
Product Marking	5 , Type, Rated current, Rated Voltage,

Certification marks

Soldering Methods	Wave Soldering Profile
Solderability	235 °C / 2 sec acc. to IEC 60068-2-20, Test Ta, method 1
Resistance to Soldering Heat	260 °C / 5 sec acc. to IEC 60068-2-20, Test Tb, method 1A

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: SUT 6.3x32 Pigtail

Approval Logo	Certificates	Certification Body	Description
	UL Approvals	UL	UR File Number: E184831

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
(UL)	Designed according to	UL 248-14	Low voltage fuses - Part 14: Additional fuses
GSA Group	Designed according to	CSA22.2 No. 248.14	Low-Voltage Fuses - Part 14: Supplemental Fuses

SUT 6.3x32 Pigtail

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements


Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
50	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]






In ≤ 30 A: ØA = 1.0 mm In ≥ 40 A: ØA = 1.2 mm

Pre-Arcing Time

Rated Current In	1.0 x In min.	1.35 x In max.	2.0 x In min.	2.0 x ln max.
12 A - 30 A	4 h	60 min	5 s	60 s

Time-Current-Curves



All Variants

Rated Cur- rent [A]	Rated Vol- tage [VAC]	Breaking Capacity	Voltage Drop 1.0 I _n typ. [mV]	Cold Resistance typ. [mΩ]	Melting I ² t 10.0 I _n typ. [A ² s]	c '91 1'us	Order Number
12	250	1)	78	5.6	72	•	8020.0603.PT
15	250	1)	81	4.7	152	•	8020.0604.PT
20	250	1)	87	3.6	750	•	8020.0605.PT
25	250	1)	62	2.1	1010	•	8020.0606.PT
30	250	1)	64	1.8	2050	•	8020.0607.PT

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

1) 500 A @ 250 VAC, 10 kA @ 125 VAC

Packaging Unit

Bulk (100 pcs.)