

## Scissor-type lifting table carriage

Fixed sliding handle, sturdy variant

fetra  
Transportgeräte

### Execution:

- Profile steel/sheet steel construction
- Strong tubular push handle, firmly screwed-in
- Hydraulic pump with chrome-plated piston
- Actuated by foot pedal
- Use the hand lever to actuate the lowering valve sensitively
- 2 castors and 2 fixed castors, polyurethane tyre wheels,
- steering wheels with locking device
- Powder-coated, anthracite RAL 70 16

<b>Art. no.</b>	<b>50262 915</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	6833
<b>Load-carrying capacity</b>	500 kg
<b>Min. table height</b>	435 mm
<b>Max. table height</b>	1000 mm
<b>Loading surface length</b>	1010 mm
<b>Loading-surface width</b>	520 mm
<b>Wheel diameter</b>	150 mm
<b>Material of wheel</b>	Polyurethane
<b>Length</b>	1275 mm
<b>Width</b>	520 mm
<b>Total stop optional</b>	No
<b>Gross Weight</b>	115.000 kg
<b>Product Group</b>	5AE



### EAN

4017976068336