



Kegelsenker 90° DIN 335 C Countersink 90° DIN 335 C

EXACT
PRÄZISIONSWERKZEUGE

HSS | HSS



Technische Information

HSS = Hochleistungsschnell-Stahl
DIN 335 C • Mit Zylinderschaft + 3 Schneiden

Technical Information

HSS = High-speed-steel
DIN 335 C • With cylindrical shaft and 3 flutes

Anwendung

Zum Senken und Entgraten

Application

For deburring and countersink

| mm | DIN 74 | | DIN 75 | | mm | mm | mm | CODE | € | CODE | € | CODE | € | CODE | € |
|------|--------|-------|--------|-------|----|----|-----|-------|---|-------|-------|------|-------|------|---|
| | AF | SF | AF | SF | | | | | | | | | | | |
| 4,3 | M 2 | M 1,8 | M 2 | | 40 | 4 | 1,3 | 05501 | | 05541 | | | | | |
| 5,0 | M 2,5 | M 2 | | | 40 | 4 | 1,5 | 05502 | | 05542 | | | | | |
| 5,3 | | | M 2,6 | M 2,6 | 40 | 4 | 1,5 | 05503 | | 05543 | | | | | |
| 5,8 | | | M 3 | | 45 | 5 | 1,5 | 05504 | | 05544 | | | | | |
| 6,0 | M 3 | M 2,5 | | | 45 | 5 | 1,5 | 05505 | | 05545 | | | | | |
| 6,3 | | M 3 | M 3,5 | M 3 | 45 | 5 | 1,5 | 05506 | | 05546 | 51106 | | 51136 | | |
| 7,0 | M 3,5 | M 3 | | | 50 | 6 | 1,8 | 05507 | | 05547 | | | | | |
| 7,3 | | | M 4 | M 3,5 | 50 | 6 | 1,8 | 05508 | | 05548 | | | | | |
| 8,0 | M 4 | M 3,5 | | | 50 | 6 | 2,0 | 05509 | | 05549 | | | | | |
| 8,3 | | M 4 | | M 4 | 50 | 6 | 2,0 | 05510 | | 05550 | 51110 | | 51140 | | |
| 9,4 | | | M 4 | | 50 | 6 | 2,2 | 05511 | | 05551 | | | | | |
| 10,0 | M 5 | M 4 | | | 50 | 6 | 2,5 | 05512 | | 05552 | | | | | |
| 10,4 | | M 5 | M 6 | M 5 | 50 | 6 | 2,5 | 05513 | | 05553 | 51113 | | 51143 | | |
| 11,5 | M 6 | M 5 | | | 56 | 8 | 2,8 | 05514 | | 05554 | | | | | |
| 12,4 | | M 6 | | M 6 | 56 | 8 | 2,8 | 05515 | | 05555 | 51115 | | 51145 | | |
| 13,4 | | | M 8 | | 56 | 8 | 2,9 | 05516 | | 05556 | | | | | |
| 15,0 | M 8 | M 6 | | | 60 | 10 | 3,2 | 05517 | | 05557 | 51117 | | | | |
| 16,5 | | M 8 | M 10 | M 8 | 60 | 10 | 3,2 | 05518 | | 05558 | 51118 | | 51148 | | |
| 19,0 | M 10 | M 8 | | | 63 | 10 | 3,5 | 05519 | | 05559 | | | | | |
| 20,5 | | M 10 | | M 10 | 63 | 10 | 3,5 | 05520 | | 05560 | 51120 | | 51150 | | |
| 23,0 | M 12 | M 10 | | | 67 | 10 | 3,8 | 05521 | | 05561 | | | | | |
| 25,0 | | M 12 | | M 12 | 67 | 10 | 3,8 | 05522 | | 05562 | 51122 | | 51152 | | |
| 28,0 | | M 14 | | M 14 | 71 | 12 | 4,0 | 05523 | | 05563 | | | | | |
| 30,0 | | M 16 | | | 71 | 12 | 4,2 | 05524 | | 05564 | | | | | |
| 31,0 | | | | M 16 | 71 | 12 | 4,2 | 05525 | | 05565 | 51125 | | 51155 | | |
| 40,0 | | | | M 24 | 80 | 15 | 5,0 | 05526 | | 05566 | | | | | |

Weitere Abmessungen für TiCN + TiAlN auf Anfrage | Other sizes available on request