

Solid carbide deburring tool for interchangeable head system
6 cutting edges, TiAlN-coated



Application

For cutting chamfers and deburring on machining centres and CNC machines.

Execution

- Solid carbide ultra-fine grain
- Type N
- 90°
- TiAlN-coated



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas- tics	Graphite G(C)FK	GG(G) GJMW	Titan- alloy	Nickel- alloy	Super- alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	170	120	110	110				290	310	290	310			140					

Art. No.	16983 116
Cutting material	VHM
Chamfer angle	90 Degree
Twist angle	0°
Cutting edge diameter	16 mm
Cutting edge length	12 mm
Length	21 mm
fz steel 1000	0.07 mm

EAN-Code

4050293406863