

ER collet chuck

In accordance with ISO 12164 (DIN 69893)

ORION[®]

Application:

For clamping tools with straight shanks in ER collet chucks in line with DIN 6499.

Execution:

- With Balluff chip hole.
- All functional surfaces machined.
- All ER16 collet chucks feature a hexagon nut.

Delivery:

1x ER collet chuck in accordance with ISO 12164 (DIN 69893); incl. clamping nut.



Art. no.	23296 181
Brand	ORION
Manufacturer Part Number	23296181
Tool holding device	HSK 63
Collet type	ER 16
Min./max. clamping range	0.5-10 mm
Projecting length	160 mm
Outer diameter	32 mm
Balancing quality	G 6,3 at 20 rpm
Gross Weight	1.247 kg
Product Group	2AV

EAN

4053625294947