

Flat-bed hand truck, 2-axle with towing eye

Open, carrying capacity 700 kg to 1250 kg

fetra
Transportgeräte

Execution:

- Modular system
- From welded profile steel, 4 tubular sleeves at corners
- Scissors-shaped drawbar with safety handle with soft rubber grip and with an automatic damped retraction in resting position
- Load area covered with slip-resistant phenolic resin coated waterproof plywood
- Wheels either with solid rubber or air tyres, hubs with roller bearings
- Automatic locking brake acting on the front wheels, according to EN 1757-3
- Drawbar eye, internal diameter 32 mm
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant



| | |
|---------------------------------|------------------|
| Art. no. | 50267 864 |
| Brand | FETRA |
| Manufacturer Part Number | 6405LZ |
| Length | 1945 mm |
| Height | 1200 mm |
| Loading surface length | 1600 mm |
| Width | 900 mm |
| Loading-surface width | 900 mm |
| Loading surface size | 1600 x 900 mm |
| Loading-surface height | 490 mm |
| Load-carrying capacity | 1000 kg |
| Total stop optional | No |
| Wheel width | 100 mm |
| Wheel diameter | 400 mm |
| Material of wheel | Air |
| Gross Weight | 78.000 kg |
| Product Group | 5AE |

EAN

4017976214054