


RFSMAA2JEGIDHB Datasheet

Product Name // SMA Straight Jack 2 Hole Flange RF Connector

[View Product Page](#)



// Product Description:	
⊗ SMA Straight Jack 2 Hole Flange RF Connector	⊗ Dielectric withstanding Voltage: >750V
⊗ Maximum Voltage: 335V	⊗ Impedance: 50Ohm
⊗ Temperature range: -65Å°C to +165Å°C	⊗ Body Material: Stainless Steel Passivation
⊗ Frecuency range: 0GHz - 18GHz	⊗ Contact Material: Beryllium Copper
⊗ VSWR:	

// General Information:	
Product Display Title:	SMA Series Pin with Extended PTFE 2 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	SMA Series
Body Length:	9.40mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Coupling Nut Retention Force:	>27.2Kg
Dielectric Withstanding Voltage:	>750V
Durability:	>500 cycles
Flange Mount Length:	15.80mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710
Max Operating Temperature:	+165°C
Min Operating Temperature:	-65°C
Mount Hole Distance:	12.20mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	18GHz
Pin Diameter:	1.00mm
Pin Length:	1.50mm
Ptfe Diameter:	4.10mm
Ptfe Length:	3.00mm
Thread Size:	1/4 36UNS 2A
Voltage Max:	335V
Vswr:	<1.30

// Product PDF Links

[SMA Series Product Datasheet](#)