

**Description: C14G-HARSJT3x18AWG-C13/1,5M BLACK**

Rating of cord set: 10A/250Vac

**1. PLUG: Type C14G**

Interconnection coupler according to : EN/IEC 60320-2-2/E, UL 817, C22.2No.21, JISC8303, GB17465.1  
Rated current and voltage : 10 A, 250 V AC  
13 A, 250 V AC (USA, CANADA)  
15 A, 250 V AC (USA, CANADA, JAPAN)  
Plugbase : PPO GFR  
Pins : solid brass, nickel-plated, crimped  
Pins dimension : 4,00mm x 2,00mm  
Outer mold : PVC compound, hardness Shore A75-77  
Approvals : CE, ENEC, SAA, UL, CSA, PSE, CCC

**2. CORD: Type HARSJT3x18AWG**

Flexible cord according to : UL62, CSA 22.2No49, ÖVEK41a, HD21.5 S3:1994/A2:2001, AS3191, 6B5023, JIS C3306, IEC 60227  
Marked : \*JF\* <ÖVE> <HAR> H05VVVF3G1, 0\*CE\*N1095\*UL  
\*E41542\*CSA\*LL15075\*SJT3x18AWG\*FT2\*CCC227  
IEC53(RVV)300/500V 3x1,0\*<PS>E\*JET\*HVCTF 75°C  
Number of cores : 3  
Conductor construction : 31x0,2 mm O.D. 1,25mm  
Conductor insulation : Extruded PVC O.D. 2,80mm  
Jacket : Extruded PVC O.D. 7,60mm +/- 0,20mm  
Temperature rating : HAR -20°C up to +75°C// UL -20°C up to +60°C  
El. Resistance of conductors : max. 19,5 Ω/km  
Dielectric strength : 2kVac, 1min.  
Insulation resistance : >0,010MΩ/km  
Color of conductors : yellow/green, brown, blue  
Approvals : HARMONIZED, ÖVE, SAA, UL, CSA, CCC, PSE (JET)

**3. CONNECTOR: Type C13**

Molded connector according to : EN/IEC60320/C13, UL817, C22.2No.21, GB17465.1, JIS C8303  
Rated current and voltage : 10 A, 250 V AC  
10 A, 125 V AC (USA, CANADA)  
Construction : double insulation  
Contacts of the connection : self-adjusting phosphor bronze CuSn6  
Inner insulation : PPO GFR  
Outer mold : PVC compound, hardness Shore A 75-77  
Approvals : CE, ENEC, SAA, UL, CSA, CCC, PSE (JET), SII

**Environmental conformity**


: EU-Directive 2002/96/EC (WEEE)  
EU-Directive 2003/11/EC (Council Directive 76/769/EEC)  
EU-Directive 2002/95/EC (RoHS-compliant)

**TESTING**

Electrical testing : 100%  
Visual inspection : 100%  
High pot test wire to wire : 3kVac for 2 sec.  
Continuity test : 25Aac to grounding / 20Aac to line and neutral  
Polarity test : yes  
Skin high pot test : 6kVac line to skin

Tolerances not indicated in the drawing: +/- 2 %  
design subject to change without prior notice

DATE of ISSUE:	January 2012		
REV: 1	1	ORIG:	lg



**Feller Type: C14G-HARSJT3x18AWG-C13/1,5M BLACK**

**FELLER** 

A-2525 Günselsdorf, Austria

Telefon 0043-2256-62325-0

Fax: 0043-2256-62325-7

email: [sales@feller-at.com](mailto:sales@feller-at.com)

<http://www.feller-at.com>

**All dimensions in mm**

**RoHS compliant**

**25.01.12**

**lg**