

ELECTRONIC THERMOSTAT ETR011 AC 120 V, -4 TO +140 F



Figure similar

Model		
product brand name		SIVACON
Product designation		thermostat
<b>Design of the switching function</b>		CO contact
General technical data		
Operating temperature / minimum	°C	-45
<b>Mechanical service life (switching cycles) / typical</b>		50 000
Voltage		
<b>Inrush current / typical</b>	A	8
Main circuit		
Operating voltage / Rated value	V	120
Operating current / Rated value	A	8
Product details		
<b>Product component</b>		
• digital display		No
• hygostat		No
Mechanical Design		
<b>Height</b>	mm	64.5
<b>Width</b>	mm	42
<b>Depth</b>	mm	38
<b>Mounting type</b>		terminal mounting
Material / of the enclosure		plastic
Environmental conditions		

Relative humidity / Reference value	%	90
<b>Ambient temperature</b>		
• during storage / minimum	°C	-45
• during storage / maximum	°C	85

## Certificates

### Equipment marking

- |                          |   |
|--------------------------|---|
| • acc. to DIN EN 61346-2 | K |
| • acc. to DIN EN 81346-2 | K |

## General Product Approval



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21701GB>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21701GB/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR21701GB](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21701GB)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015