



Technical Data Sheet

Product Data Sheet for KleenGuard® A40 Liquid & Particle Protection Coveralls - Hooded / White

Product Information

Customer Facing Code 97900 - 97950

Description KleenGuard® A40 Liquid & Particle Protection

Coveralls - Hooded / White

PDS Reference 17/03/2020 Status On Sale



Packaging Configuration

Case Contents 97900: 25 Garments

97910: 25 Garments 97920: 25 Garments 97930: 25 Garments 97940: 25 Garments 97950: 25 Garments

Outer Pack Material Corrugated

Packad	ing and	d Pall	letisation

Code/Size	ITF Barcode	EAN Barcode	Case LWH (cm)	Net/Gross Weight (kg)		Pallet LWH (m)	Cases per Pallet	Inner Gross Weight (Kg)
97900-S	10036000097907	036000097900	40 x 30 x 34	5.45/6.36	E5	1.20 x 0.80 x 1.17	8 x 3 =24	0.23
97910-M	10036000097914	036000097917	40 x 30 x 34	6.95/7.87	E5	1.20 x 0.80 x 1.17	6 x 3 =18	0.30
97920-L	10036000097921	036000097924	40 x 30 x 36	7.15/8.08	E5	1.20 x 0.80 x 1.23	6 x 3 =18	0.30
97930-XL	10036000097938	036000097931	40 x 30 x 36	7.73/8.66	E5	1.20 x 0.80 x 1.23	6 x 3 =18	0.32
97940-XXL	10036000097945	036000097948	40 x 30 x 39	8.01/8.97	E5	1.20 x 0.80 x 1.32	6 x 3 =18	0.33
97950-XXXL	10036000097952	036000097955	40 x 30 x 39	8.31/9.27	E5	1.20 x 0.80 x 1.32	6 x 3 =18	0.35

Product Description

KleenGuard* A40 coveralls are designed for single-use wear and provide maximum comfort and protection in high-risk areas where safety and flexibility is key. Each coverall provides general protection against water-based or chemical splashes, liquids or dust particles with the added benefit of anti-static protection and is supplied in a sealed clear polybag for protection which comes with concise user instructions. With a specially designed hood, body, thumb loops and waist for comfort, safety and strength, these coveralls are the protection clothing of choice for industry professionals across the globe, providing PPE Category III protection and the following performance requirements:• Type 5 Particle protection• Type 6 Limited splash protection• EN1073-2 Radioactive dust• EN1149 Anti-staticldeal for users working in chemical and pharmaceutical industries, manufacturing, utilities, electronics, agriculture and paint spraying areas. For other coverall sizes, see product codes 97900, 97910, 97920, 97930 and 97940. 25 x 1 white coverall, 3XL, (25 total)

Product Data Sheet for KleenGuard® A40 Liquid & Particle Protection Coveralls -Hooded / White

Features and Benefits

Features Benefits

Offering protection to the levels specified for Type 5 & 6 by CEN Approved as Complex Design (Category 3) equipment

Ideal for protecting against powders, larger fibres and protection

against a wide range of chemicals

Suitable for use as protection against solid particles and

particulate radioactive contamination

To EN 1149-5 Treated to be antistatic

Suitable for tasks such as paint spraying cars and clean room Ultra low lint fabric

environments

EN1073-2

Reducing contamination in critical areas, Working in working in

pharmaceutical industries, manufacturing, utilities, electronics

Product Configuration

Technology Film laminate Low lint Yes **Breatheable** No Sterile No **Latex Free** Yes Silicone Free Yes Colour White Lightweight No

International Standards and Symbols

Marketing

Fabric Choice

Technology - Apparel



Solution

We know staff safety is your top priority. You can rely on our solutions

to protect them, their environment and your important work.



Productive Workplace

Safer Workplace

The success of your business hinges on your work efficiency. That's why our solutions are designed to help improve your productivity.



Standard R+E

Workwear Type 5

EN ISO 13982-1:2004 -**Particle Protection**



Workwear Type 6

EN 13034:2005 - Limited **Splash Protection**



Radioactive Dust Contamination Protection

EN 1073-2:2002



Product Data Sheet for KleenGuard® A40 Liquid & Particle Protection Coveralls - Hooded / White

Chemical Protection

Chemical Protection



Antistatic

EN 1149-1:1995



Simple - CAT I, Intermediate - CAT II or Complex - CAT III

CE Mark



Apparel

Case

40 x 30 x 39

Range Symbol



Trade

ISO 9001

Unit Of Sale

Case Dimension(LXWXH)(cm)

This gives the requirements for quality management systems, is now firmly established as the globally implemented standard for providing assurance about the ability to satisfy quality requirements and to enhance customer satisfaction in supplier-customer relationships.



Test Results

Test	Result
-EN ISO 13935-2 Seam Strength (Grab test)	Class 3 of 6
EN ISO 13982-2 - Particle Inward Leakage (taped at the hood, wrist & ankles)	PASS
EN1149-5 - Antistatic	PASS
BS EN 863:1996 - Puncture resistance	Class 2 of 6
EN 1073-2 - Radioactive dust	Class 1
EN 13274-4 M3 - Resistance to Ignition	PASS
EN 530 M2 - Abrasion Resistance	Class 6 of 6
EN ISO 13934-1 - Tensile Strength	Class 2 of 6
EN ISO 17491-4 (modified) - Resistance to Penetration by Liquids (spray test)	PASS
EN ISO 7854 MB - Flex Cracking	Class 4 of 6
ISO 6530 - Repellency to Liquid Chemicals	10%NaOH , 30%H2SO4, Class 3 of 3
ISO 6530 - Resistance to Penetration by Liquid Chemicals	10%NaOH , 30%H2SO4, Class 3 of 3
ISO 9073-4 - Trapezoidal Tear Resistance	Class 2 of 6

Packaging

Inner Pack Material

10.51

Mixed Plastic

Max Weight(kg)

Product Data Sheet for KleenGuard® A40 Liquid & Particle Protection Coveralls - Hooded / White

I I O O I	- 101	○ †1	$\alpha n c$	1
Inst				١

Do not use chlorine - based bleach.

Do not dry clean.

Inflammable. Keep away from open flames, sparks or intense heat sources. The fabric will begin to melt at the approximate temperature indicated.

The open book pictogram - indicates that the user should read and understand the USER INSTRUCTIONS before using the garment.

Do not iron.

Do not tumble dry

Do not wash.

Information

It is the employer's responsibility to assess the risk of the task to be undertaken and determine the correct choice of personal protective equipment for the task. The manufacturer, Kimberly-Clark, does not accept any responsibility for the incorrect choice or misuse of the personal protective equipment shown in this brochure. All care has been taken to ensure that the information contained herein is as accurate as possible at the time of publication, however errors may occur and legislation concerning personal protective equipment is under constant review and may change in the lifetime of this brochure. Accordingly, the specification for the products may be subject to change. We would advise you to contact INFOFAX if you have any queries concerning the products shown or the suitability of such products for a particular task. Always dispose of used protective equipment in a safe and appropriate manner in accordance with European, National and Local environmental regulations.

Websites www.kcprofessional.co.uk Storage conditions Keep dry. Store in a cool dry place and

shield from exposure to direct sunlight, intense artificial light or exposure to sources of radiation or ozone.

Durability This product has an unlimited

shelf life.

Customer Service Number

For more information please contact Customer Service during regular office hours-0870 551 044

Country of Origin CHINA