

Angle standard 90°, triangular form

Highest accuracy



Application:

For simple and precise checking of the 90° angle. Ideal for use on hard stone bases, e.g. for checking straightness in vertical height measuring devices; also suitable as a contact surface for large components. Also suitable for checking the 90° angle e.g. in coordinate measuring instruments and machine tools.

Execution:

- Carefully selected and flawless South African hard stone material – Diabas.
- with through-bore(s) for weight reduction
- Exactly 2-sided. The two precisely shaped surfaces are finely machined to a high-quality finish to be flat and at exact angles to one another. The remaining surfaces are finely machined
- LAB accuracy: surface finely ground and lapped to maximum fineness
- can be used horizontally and vertically
- Calibration certificate included in the scope of delivery. measurement results are based on national standards
- DAkkS calibration certificate available on request

Delivery:

Calibration certificate. Measurement results are based on national standards from the German National Metrology Institute in Brunswick, Germany.



Art. no.	35283 030
Brand	JFA
Limb length	300 mm
Limb length 2	200 mm
Width	50 mm
Number of drill holes	1 PCS
Weight	6 kg
JFA precision LAB	0.001 mm
Gross Weight	6.000 kg
Product Group	341