

Microswitches

Order code	Manufacturer code	Description
78-0735	n/a	MICROMINIATURE LEVER SWITCH

Microswitches	Page 1 of 3
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

1. Mechanical Specifications



Shock Resistance	:	100g
Max. Operating Frequency	:	200 Operations/Min
Service Life	:	Min 10,000,000 Operations
Operating Force (OF)	:	Max. 50g
Releasing Force (RF)	:	Min 8g
Operating Position (OP)	:	8.4 ± 0.8mm
Movement Differential (MD)	:	Max. 0.8mm
Free Position (FP)	:	Max. 11mm
Overtravel (OT)	:	Min. 0.6mm
Pretravel (PT)	:	Max. 3.4mm

2. Electrical Specification

Rating	:	3A 125V _{AC}
Contact Resistance	:	Max. 30 M ohms. (Initial)
Insulation Resistance	:	Min 100 M ohms (at 250V _{DC})
Service Life	:	Min 30,000 on resistive load current 3A 125V _{AC}
Max. Operating Frequency	:	30 operations/min.
Shock Resistance	:	30 g

3. Durability Specification

Ambient Temperature	:	-25°C to +85°C
Ambient Humidity	:	Max. 85% RH.
Solder Dip Time	:	Within 5 Sec. at 250 ± 5°C



UNIT :MM

Tolerance ± 0.4