










## **Model Number**

NBB5-18GM40-Z3-V1

## **Features**

- 5 mm flush
- 2-wire DC

## Connection



## **Pinout**



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

## **Accessories**

Mounting flange, 18 mm

V1-G

4-pin, M12 female field-attachable connector

V1-W

4-pin, M12 female field-attachable connector V1-G-2M-PUR


Cable socket, M12, 4-pin, PUR cable V1-W-2M-PUR

Cable socket, M12, 4-pin, PUR cable **EXG-18** 

www.pepperl-fuchs.com

Quick mounting bracket with dead stop

## **Dimensions**



# **Technical Data**

General specifications			
Switching element function		DC	NO
Rated operating distance	s <sub>n</sub>	5 mm	
Installation		flush	
Output polarity		DC	
Assured operating distance	sa	0 4.0	5 mm
Reduction factor r <sub>Al</sub>		0.34	
Reduction factor r <sub>Cu</sub>		0.31	
Reduction factor rand		0.72	

Nominal	ratings

Nominal ratings		
Operating voltage	$U_B$	5 60 V
Switching frequency	f	0 500 Hz
Hysteresis	Н	1 10 typ. 5 %
Reverse polarity protection		tolerant
Short-circuit protection		pulsing
Voltage drop	$U_d$	≤ 5 V
Operating current	IL.	2 100 mA
Lowest operating current	I <sub>m</sub>	2 mA
Off-state current	l <sub>r</sub>	0 0.5 mA typ.
Indication of the switching state		Multihole-LED vellow

#### Functional safety related parameters

MTTF <sub>d</sub>	1870 a
Mission Time (T <sub>M</sub> )	20 a
Diagnostic Coverage (DC)	0 %

# Ambient conditions

Ambient temperature -25 ... 70 °C (-13 ... 158 °F)

## Mechanical specifications

Mechanical Specifications	
Connection type	Device connector M12 x 1 , 4-pin
Housing material	brass, nickel-plated
Sensing face	PBT
Protection degree	IP67

### Compliance with standards and directives

#### Standard conformity

Standards	EN 60947-5-2:2007
	IEC 60947-5-2:2007

#### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose

Certified by China Compulsory Certification (CCC) CCC approval