


**Model Number**

NCB15-30GM50-Z4

Features


- 15 mm flush
- 2-wire DC
- Increased operating distance

Connection**Accessories****BF 30**

Mounting flange, 30 mm

EXG-30

Quick mounting bracket with dead stop

Dimensions**Technical Data****General specifications**

Switching element function		DC	NO
Rated operating distance	s_n	15 mm	
Installation		flush	
Output polarity		DC	
Assured operating distance	s_a	0 ... 12 mm	
Reduction factor r_{Al}		0.4	
Reduction factor r_{Cu}		0.4	
Reduction factor r_{304}		0.7	
Reduction factor r_{Brass}		0.5	

Nominal ratings

Operating voltage	U_B	3.5 ... 30 V
Switching frequency	f	500 Hz
Hysteresis	H	typ. 5%
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_d	≤ 3.5 V
Temperature drift		$\pm 15\%$
Operating current	I_L	2 ... 100 mA
Off-state current	I_r	typ. 0.8 mA
Switching state indication		LED, yellow
Pre-fault indication		LED, red
Stability control-switch point		0,8 s_r ... 0,9 s_r

Functional safety related parameters

MTTF _d	1390 a
Mission Time (T_M)	20 a
Diagnostic Coverage (DC)	0 %

Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
Storage temperature	-25 ... 85 °C (-13 ... 185 °F)

Mechanical specifications

Connection type	cable PVC, 2 m
Core cross-section	0.34 mm ²
Housing material	brass, nickel-plated
Sensing face	PBT
Protection degree	IP67


Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	CCC approval / marking not required for products rated ≤ 36 V

Correlation between output signal/LED-function and stable operating distance s_s / effective operating distance s_r : (s_s typ. 80 % of s_r)



Release date: 2013-05-16 11:31 Date of issue: 2013-05-16 127392_eng.xml