



HEAT EXCHANGER;80W PER K AIR AIR SPEC.  
THERMINAL CAPACITY. 80W PER K 317X1260X108  
MM (WXHXD) DEGREE OF PROTECTION IP 54

Figure similar

Model		
product brand name		SIVACON
Product designation		air-air heat exchanger
Design of the temperature control		without thermostat
Main circuit		
<b>Operating voltage</b>		
• with AC / at 50 Hz / Rated value / maximum	V	230
• with AC / at 60 Hz / Rated value / maximum	V	230
Product details		
<b>Product component</b>		
• Heating		No
• Thermostat		No
Mechanical Design		
<b>Height</b>	mm	1 260
<b>Width</b>	mm	317
<b>Depth</b>	mm	108
<b>Installation location</b>		Control cabinet...panels, door
Certificates		
<b>Equipment marking</b>		
• acc. to DIN EN 61346-2		E
• acc. to DIN EN 81346-2		E



#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64235ML80>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8MR64235ML80/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR64235ML80](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR64235ML80)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015