




Actuator/sensor cable, PVC
Connection cable
RSS12T-2/TEL



- Male M12, straight, 12-pin
- Shield on coupling nut/screw
- Sheath material: PVC, shielded
- Sheath color: black
- Resistant to chemicals and oils
- Flame retardant
- Resistant to acids and alkaline solutions
- Resistant to microbes and hydrolysis
- LABS free
- Approval: cULus
- RoHS conform
- Protection class IP67
- Cable length: 2.0 m


Type designation	RSS12T-2/TEL
Ident no.	6626911
Connector A side	Connector, M12 ♂ 1, Straight
Number of pins	12
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, TPU, Black
Grip	Plastic, TPU, Black
Coupling nut/screw	Brass, CuZn, Nickel-plated
Protection class	IP67, A + B side screwed together
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Tightening torque	0.8 ... 1 Nm (observe max. torque of counter piece!)
General data	
Cable diameter	6.6 ± 0.20mm
Cable length	2 m
Cable quality	PVC
Cable color	Black
Core insulation	PVC
Core colors	BN, BU, WH, GN, PK, YE, BK, GY, RD, VT, GY/PK, RD/BU
Core cross-section	12x0.14mm ²
Arrangement of strands	18x0.1 mm
Shielding	Aluminum foil, tinned copper wire

Cable Cross-section



Drawing shows design status including hexagon coupling nut (Start of production CW42/2016).

Circuit Diagram




Actuator/sensor cable, PVC
Connection cable
RSS12T-2/TEL

TURCK

Industrial
Automation

Accessories

Type code	Ident no.	Description	
Torque-Wrench-Set-AS	6936170	Torque wrench set; handles with adjustable torque 0.4-1.0 Nm, torque wrench for M8 (SW9), fork wrench for M12 (SW 14)	
BLANK-LABEL-FOR-CORDESETS-TEL-TXL	6936206	Label for TEL and TXL cables, length: 18 mm, height: 4 mm, material: polycarbonate (PC), color: white, halogen-free and flame-retardant	