

Introduction













The diameter 1.5 mm and diameter 2.5 mm Connector System is designed for electronic and electrical applications in motor vehicles.

It fullfils all requirements for a connector system for use in automobiles and covers a wide range of applications.

Contacts

- Basic material (CuNiSi) with high current capacity
- Rugged two-piece construction with stainless steel jacket
- Six points of contact (2.5 mm System) and five points of contact (1.5 mm System)
- 2.5 mm System wire range 0.2–4.0 mm²
- 1.5 mm System wire range 0.2–2.5 mm²

Connectors


- High reliability status supported for long term use
- High vibration level supported
- Perfect design to avoid quality problems, reduce manufacturing and service cost
- Integrated secondary locking device delivered in pre-locked position
- Wire-to-Wire sealed and unsealed connectors (SWS)
- Wire-to-Board sealed and unsealed connectors (SWS)

- Polarisation, several keyings
- Locking mechanism for smaller connectors/mating aid for higher numbers of ways
- Sealed Circular Connector Series (SCCS)
- Injector Connectors
- Miscellaneous Sealed Connectors for Circular Contacts

Connector System for Circular Contacts

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Engineering Notes



Circular Contact SystemsDiameter 1.5 mm and 2.5 mm Contact System

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Introduction













The diameter 1.5 mm and diameter 2.5 mm round contact systems developed by Tyco Electronics is mainly used in the automotive industry. Due to its wide range of performance possibilities, this contact system is in use in the engine compartment for aggregate or sensor connections.

Every contact has got a steel cantilever spring and a copper alloy body.

The two-piece contact design means that the electrical and mechanical properties are separated. One end of the contact body is crimped to wire and the other end mates with the matching pin.

The closed cantilever spring has got several functions and also different advantages for the complete contact system.

In addition there are several lances on the steel to spring. These serve to look the contact securely in the housing.

Sockets and pins can be applied on both sealed and unsealed connectors.

The diameter 1.5 mm and diameter 2.5 mm contact system can be fast and economically arranged to the lead using Tyco Electronics application tooling.

Technical Features

- 100 % quality assurance for the contact socket
- Resistant against fretting corrosion
- Vibration resistant
- Excellent longevity
- Low contact resistance
- High position configurations
- Contact design accepts secondary locking device
- Several contact points
- Sturdy contact design
- Guarantees constant insertion and extraction forces

Socket and Pin Contacts

Technical Features

Wire Size Range: 0.2-2.5 mm²

Insulation Diameter:

1.2-3.0 mm

Contact Material:

CuNiSi, CuNi18Zn20, CuFe2

Contact Finish:

Tin plated, silver plated, gold plated, plain

Temperature Range

-40 °C to +130 °C (tin plated) -40 °C to +140 °C (silver plated) -40 °C to +150 °C (gold plated) -40 °C to +150 °C (plain)

Current Carrying Capacity:

Up to 30 A max.

Product Specification:

108-18028

Application Specification:

114-18040

Extraction Tool:

Part No. 539972-1 (Socket Contact)

Part No. 3-1579007-7

(Pin Contact)

Spare Tube:

Part No. 5-1579007-0

(Socket Contact)


Part No. 3-1579007-8


(Pin Contact)

Terminal Mounting Tool:

(for 0.2-1.0 mm²)

Part No. 965702-1





Circular Contact SystemsDiameter 1.5 mm Contact System

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Socket Contacts

Diameter 1.5 mm Socket Contacts

Wire Size		n Diameter	Material		Part Numbers						
Range (mm²)	FLK	mm) FLR	and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator *	Hand Tool◆		
0.2-0.4	-	1.15–1.6	tin plated	929985-1	5,000	962994-1	500	878480	734285-1		
0.5.1.0		1.4–2.1	tio plated	929986-1	4,500	962995-1	500	878481	734285-1		
0.5–1.0	-	1.4–2.1	tin plated	929986-4	5,000	962995-4	500	070401	734200-1		
≥1.0-2.5	-	1.9–3.0	tin plated	929987-1	3,800	962996-1	500	878482	734285-2		

*) Contact Material:

xxx-1 = CuNiSi

xxx-4 = CuFe2

Note: All Part Numbers are RoHS and ELV compliant.

Diameter 1.5 mm Socket Contacts with Single Wire Sealing System

Wire Size		n Diameter	Makadal	Part Numbers						
(mm²)	FLK	nm) FLR	Material and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator *	Hand Tool *	
0004		1.2–2.1	tin plated	929988-1	4,000	962997-1	500	878484	734289-1	
0.2–0.4	_	1.2-2.1	silver plated	929988-2	4,000	962997-2	500	070404	734209-1	
			tin plated	929989-1	4,000	962998-1	500			
	- 1.2-2.1			silver plated	929989-7	4,000	962998-7	8-7 500		
0.5-1.0		- 1.2-2.1	gold plated	929989-8	4,000	-	-	878485	734289-1	
			plain	1-929989-0	4,000	1-962998-0	500			
			tin plated	929989-4	4,000	962998-4	500			
			tio plated	929990-1	3,800	962999-1	500			
~1005		0.0.00	tin plated	929990-4	3,800	962999-4	500	070406	704000 0	
≥1.0–2.5	_	- 2.2-3.0 -	silver plated	929990-7	3,800	962999-7	500	878486	734289-2	
			plain	1-929990-0	3,800	1-962999-0	500			

*) Contact Material:

xxx-1 = CuNiSi

xxx-2 = CuNiSi

xxx-4 = CuFe2

xxx-7 = CuNiSi

xxx-8 = CuNiSi

1-xxx-0 = CuNi18Zn20

^{*)} This Applicator and Hand Tool Part Number is only one of a part number selection. Please call your local Tyco Electronics representative for personal assistance or visit our website.

^{*)} This Applicator and Hand Tool Part Number is only one of a part number selection. Please call your local Tyco Electronics representative for personal assistance or visit our website.

Circular Contact SystemsDiameter 1.5 mm Contact System

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Pin Contacts

Diameter 1.5 mm Pin Contacts with Single Wire Sealing System

Wire Size		n Diameter	Material	Part Numbers						
Range (mm²)	FLK (r	nm) FLR	and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator *	Hand Tool *	
0.2–0.4 –		1001	tio plated	1703012-1	4,000	1703016-1	500	070404	704000 1	
	_	1.2–2.1	tin plated	1703012-4	4,000	1703016-4	500	878484	734289-1	
	- 1.2-2.1	- 1.2-2.1		tin plated	1703013-1	3,500	1703017-1	500		
0.5–1.0			silver plated	1703013-2	3,500	1703017-2	500	878485	734289-1	
0.5-1.0			- 1.2-2.1	gold plated	1703013-8	3,500	-	-	676465	734209-1
			tin plated	1703013-4	3,500	1703017-4	500			
≥1.0-2.5		2220	tin plated	1703014-1	3,500	1703018-1	500	070406	724000 0	
		- 2.2–3.0	1703014-4	3,500	1703018-4	500	878486	734289-2		

*) Contact Material:

xxx-1 = CuNiSi

xxx-2 = CuNiSi

xxx-4 = CuFe2

xxx-8 = CuNiSi

^{*)} This Applicator and Hand Tool Part Number is only one of a part number selection. Please call your local Tyco Electronics representative for personal assistance or visit our website.

Socket and Pin Contacts

Technical Features

Wire Size Range: 0.2-4.0 mm²

Insulation Diameter:

1.15-3.6 mm

Contact Material:

CuNiSi, CuFe2

Contact Finish:

Tin plated, silver plated, gold plated

Temperature Range

-40 °C to +130 °C (tin plated) -40 °C to +140 °C (silver plated) -40 °C to +150 °C (gold plated)

Current Carrying Capacity: Up to 40 A max.

 ${\bf Product\ Specification:}$

108-18027

 ${\bf Application\ Specification:}$

114-18020

Extraction Tool:


Part No. 1-1579007-8


Spare Tube:

Part No. 4-1579007-7

Terminal Mounting Tool: (for 0.2–1.0 mm²)

Part No. 3-1579007-2





Circular Contact SystemsDiameter 2.5 mm Contact System

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Socket Contacts

Diameter 2.5 mm Socket Contacts

Wire Size		n Diameter	Material		Part Numbers					
(mm²)	FLK	mm) FLR	and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator *	Hand Tool *	
0.2-0.4	-	1.15–1.6	tin plated	929969-1	3,000	962976-1	500	878480	734285-1	
			tin plated	929970-1	3,000	962977-1	500			
0.5-1.0	1.4–2.1	1.4–2.1	silver plated	929970-7	3,000	962977-7	500	878481	734285-1	
			gold plated	929970-8	3,000	962977-8	500			
			tin plated	929971-1	3,000	962978-1	500			
≥1.0-2.5		1.9–3.0	silver plated	929971-7	3,000	962978-7	500	878482	734285-2	
			gold plated	929971-8	3,000	962978-8	500			
≥2.5–4.0		2.7–3.0	tin plated	929972-1	3,000	962979-1	500	878483	734285-3	

*) Contact Material:

xxx-1 = CuNiSi

xxx-7 = CuNiSi

xxx-8 = CuNiSi

Note: All Part Numbers are RoHS and ELV compliant.

Diameter 2.5 mm Socket Contacts with Single Wire Sealing System

Wire Size		n Diameter	Meterial			Part	Numbers		
Range (mm²)	FLK	nm) FLR	Material and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator *	Hand Tool *
0.2–0.4		1.2–2.1	tin plated	929973-1	3,000	962980-1	500	878484	734289-1
			tin plated	929974-1	3,000	962981-1	500		
		_	gold plated	929974-8	3,000	962981-8	500		734289-1
0.5-1.0	-	1.2–2.1	ailyar platad	929974-7	3,000	962981-7	500	878485	
			silver plated	1-929974-4	3,000	1-962981-4	500		
		_	tin plated	929974-4	3,000	962981-4	500		
			tin plated	929975-1	3,000	962982-1	500		
≥1.0–2.5		- 2.2-3.0	gold plated	929975-8	3,000	962982-8	500	070406	704000 0
≥1.0-2.5	0–2.5 – 2.2–3.0 <u>—</u>		silver plated	929975-7	3,000	962982-7	500	- 878486 734 -	734289-2
		tin plated	_	929975-4	3,000	962982-4	500		

*) Contact Material:

xxx-1 = CuNiSi

xxx-4 = CuFe2

xxx-7 = CuNiSi xxx-8 = CuNiSi

1-xxx-4 = CuNiSi

^{*)} This Applicator and Hand Tool Part Number is only one of a part number selection. Please call your local Tyco Electronics representative for personal assistance or visit our website.

^{*)} This Applicator and Hand Tool Part Number is only one of a part number selection. Please call your local Tyco Electronics representative for personal assistance or visit our website.

Circular Contact SystemsDiameter 2.5 mm Contact System

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Pin Contacts

Diameter 2.5 mm Pin Contacts

Wire Size		on Diameter	Material			Part	Numbers		
(mm²)	FLK	mm) FLR	and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator *	Hand Tool *
0.2-0.4	_	1.15–1.6	tin plated	929962-1	3,500	962966-1	500	878480	734285-1
			tin plated	929963-1	3,500	962967-1	500		
0.5-1.0	-	1.4–2.1	gold plated	929963-8	3,500	962967-8	500	878481	734285-1
			gold plated	1-929963-0	3,500	1-962967-0	500		
~100F		1000	tin plated	929964-1	3,500	962968-1	500	070400	704005.0
≥1.0–2.5	_	- 1.9-3.0 -	gold plated	1-929964-0	3,500	1-962968-0	500	878482	734285-2
≥2.5-4.0	-	2.7–3.6	tin plated	929965-1	2,500	962969-1	500	878483	734285-3

*) Contact Material:

xxx-1 = CuNiSi

xxx-4 = CuFe2

xxx-8 = CuNiSi

1-xxx-0 = CuFe2

Note: All Part Numbers are RoHS and ELV compliant.

Diameter 2.5 mm Pin Contacts with Single Wire Sealing System

Wire Size		n Diameter	Material			Part	Numbers				
(mm²)	FLK	nm) FLR	and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator *	Hand Tool◆		
0,2-0,4		1.2–2.1	tin plated	929966-1	3,500	962970-1	500	878484	734289-1		
0.2-0.4	1.2-2.1	- 1.2-2.1	0.4 – 1.2–2.1 –	1.2–2.1	silver plated	929966-7	3,500	962970-7	500	070404	734209-1
			tin plated	929967-1	3,000	962971-1	500				
			silver plated	929967-7	3,000	962971-7	500				
0.5-1.0	_	- 1.2-2.1 <u>1-929</u>	1-929967-4	3,000	1-962971-4	500	878485	734289-1			
			gold plated	929967-8	3,000	962971-8	500				
				1-929967-0	3,000	1-962971-0	500				
			tin plated	929967-4	3,000	962971-4	500				
			tin plated	929968-1	3,000	962972-1	500				
≥1.0–2.5		0.0.00	silver plated	929968-7	3,000	962972-7	500	878486	734289-2		
≥1.0-2.5	_	- 2.2-3.0 - -	gold plated	929968-8	3,000	962972-8	500	070400	104209-2		
			tin plated	929968-4	3,000	962972-4	500				

*) Contact Material:

xxx-1 = CuNiSi

xxx-4 = CuFe2

xxx-7 = CuNiSi

xxx-8 = CuNiSi

1-xxx-0 = CuFe21-xxx-4 = CuNiSi


^{*)} This Applicator and Hand Tool Part Number is only one of a part number selection. Please call your local Tyco Electronics representative for personal assistance or visit our website.

^{*)} This Applicator and Hand Tool Part Number is only one of a part number selection. Please call your local Tyco Electronics representative for personal assistance or visit our website.

Single Wire Seals and Sealing Plugs

Technical Features

- 1.5 mm and 2.5 mm system accomodates insulation diameters of 1.2–3.7 mm
- Made from silicon rubber material
- Wire seal is crimped simultaneously with the contact



Diameter 1.5 mm Pin and Socket Contact

	n Diameter mm)	Color	Part Number	Package	
FLK	FLR			Quantity	
			828904-1	1,000	
_	1.2–2.1	Light Blue	828904-2	10,000	
			828904-3	5,000	
-	2.2–3.0	White	828905-1	10,000	
Cooli	ng Plug	Natural	828922-1	10,000	
Seall	ng Plug	Green	828922-2	10,000	

Diameter 2.5 mm Pin and Socket Contact

	n Diameter nm)	Color	Part Number	Package Quantity	
FLK	FLR	1.2–2.1 Gray 828920-1 Violet 828921-1		Quantity	
_	1.2–2.1	Gray	828920-1	5,000	
	2.2–3.0	Violet	828921-1	5,000	
_	2.2-3.0	Yellow	828921-2	5,000	
Sealing Plu	ug for cavities	Natural	828922-1	10,000	
up to diamet	er 3.0 mm wire	Green	828922-2	10,000	
	ug for cavities er 3.7 mm wire	Natural	828986-1	5,000	

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Introduction













The diameter 1.5 mm and diameter 2.5 mm Connector System offers receptacle and pin housings with capability for waterproofing and resistance to conditions of extreme vibration.

The system is designed for electronic and electrical applications in motor vehicles, where vibrations and mechanical stress, in the long term, can affect the quality on the contacts system.

Features

- High reliability status supported for long term use
- High vibration level supported
- Perfect design to avoid quality problems, reduce manufacturing and service cost
- Integrated secondary locking device delivered in pre-locked position
- Wire-to-Wire sealed and unsealed connectors (SWS)
- Wire-to-Board sealed and unsealed connectors (SWS)
- Polarisation, several keyings
- Locking mechanism for smaller connectors/mating aid for higher numbers of ways

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Diameter 2.5 mm Connector Housings according ISO 15170 (DIN 72585)

Technical Features

 $\hbox{No. of Positions:} \\$

2-4 Positions

Housing Material:

PBT GF 30 / PA 46-GF 30

Wire Size Range: 2.5 mm² Max.

Product Specification:


108-18621

Application Specification:

114-18255-0

 ${\bf Product\ Group\ Drawing:}$

1355392



Socket Housings

No. of	V	ving Housing -			Part Numbers		
No. of Positions	Keying Options	Color	Socket Housing	Cover	Mating Pin Housing	Mating PCI Right-Angle	3 Header Vertical
2			1-967325-3	*	1-967402-3		
3	1	Black	1-967325-2	*	1-967402-2	_	-
4			1-967325-1	*	1-967402-1	_	
2			2-967325-3	*	2-967402-3		
3	2	Gray	2-967325-2	*	2-967402-2	-	-
4			2-967325-1	*	2-967402-1	-	
2			3-967325-3				
3	3	Green	3-967325-2	*	-	_	-
4			3-967325-1				
2			4-967325-3				
3	4	Blue	4-967325-2	*	-	_	-
4			4-967325-1				

^{*)} Suitable Covers/Adapters see Accessories.

Diameter 2.5 mm Connector Housings according ISO 15170 (DIN 72585)

Technical Features

No. of Positions:

2-4 Positions

Housing Material:

PBT GF 20

Wire Size Range:

2.5 mm² Max.

 $\label{lem:product Specification:} \textbf{Product Specification:}$


108-18621

Application Specification:

114-18255-0

Product Group Drawing:

1355392



Pin Housings

No. of	Vi	Housing			Part Numbers			
No. of Positions	Keying Options	Color	Pin Housing	Cover	Mating Socket Housing	Mating PC Right-Angle	B Header Vertical	
					1-967325-3			
2			1 067400 0		1-967325-2	•		
			1-967402-3	*	1-967325-1	•		
3	1	Black	1-967402-2	*	6-968968-3	-	_	
4			1-967402-1		6-968968-2	•		
					6-968968-1	•		
2			2-967402-3		2-967325-3			
3	2 –	Gray	2-967402-2	*	2-967325-2	_	-	
4	_		2-967402-1		2-967325-1	•		

^{*)} Suitable Covers/Adapters see Accessories.

Technical Features

No. of Positions:

4 Positions

Housing Material:

PBT GF 20

Material and Finish:

CuZn, tin plated


Wire Size Range:

2.5 mm² Max.

Product Specification:

108-18621

Application Specification:



Pin Housings

No. of	Vi	Harrian.		Part Numbers					
No. of Positions	Keying Options	Housing Color	Pin Housing with Ferrite Disc	Cover	Mating Socket Housing	Mating PCI Right-Angle	3 Header Vertical		
4	1	Black	1703780-1	-	1-967325-1 or 1-968968-1	-	-		

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Diameter 2.5 mm Connector Housings according ISO 15170 (DIN 72585)

Technical Features

No. of Positions: 2–4 Positions


Housing Material: PBT GF 30 / PA 46-GF 30

Wire Size Range: 2.5 mm² Max.

Product Specification: 108-18621

Application Specification: 114-18255-0

Product Group Drawing: 1355392



Socket Housings with Secondary Locking

No. of	Varian	Ususina			Part Numbers		
No. of Keying Positions Options	Housing Color	Socket Housing	Cover	Mating Pin Housing	Mating PCI Right-Angle	3 Header Vertical	
2			1-968968-3	*	1-967402-3		
3	1	Black	1-968968-2	*	1-967402-2	_	-
4			1-968968-1	*	1-967402-1	_	
2	2	Gray	2-968968-3	*	2-967402-3		

^{*)} Suitable Covers/Adapters see Accessories.

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 - Issued 3-2010

Pin Housings, Solder Type according ISO 15170 (DIN 72585)

Technical Features

No. of Positions: 2/4 Positions

Housing Material:

PBT GF 20


Material and Finish:

CuZn, tin plated CuZn, gold plated

Product Specification:

108-18621

Application Specification:



Pin Housing

N	No. of Keying Positions Options						
No. of Positions			Right-Angle Pin Housing	Vertical Pin Housing with Ventilation Disk	Contact Plating	Mating Socket Housing	
				1394324-1	Tin	967325 or	
2/4	1	Black	-	1394324-2	Tin	968968	
				1394324-3	Gold	_	
3	2	Gray	_	1394324-4	Gold	_	

Note: All Part Numbers are RoHS and ELV compliant.

Technical Features

No. of Positions: 4 Positions


Housing Material: PBT GF 20

Material and Finish: CuZn, gold plated

Product Specification:

108-18621

Application Specification:



Pin Housing

No. of	V avrim m	Hausina		Part Numbers	
No. of Positions	Keying Options	Housing Color	Right-Angle Pin Housing	Vertical Pin Housing	Mating Socket Housing
4	1	Black	-	1241598-1	967325 or 968968

Diameter 1.5 mm Connector Housings

Technical Features

No. of Positions: 5–7 Positions

Housing Material: PBT GF 30 / PA 46-GF 30

Wire Size Range:

2.5 mm² Max.

 $\label{lem:product Specification:} Product \ Specification:$


108-18622

Application Specification:

114-18255-0

Product Group Drawing:

1355392



Socket Housings

No. of	V	Harrain n			Part Numbers		
No. of Positions	Keying Options	Housing Color	Socket Housing	Cover	Mating Pin Housing	Mating PCI Right-Angle	Header Vertical - -
5	А	Black	967650-3	*	1718230-3	-	-
	6 ^	Black	967650-2	*	1718230-2		
6	А	DIACK	967650-4	*	-		Vertical
	۸	Black	967650-1	*	1718230-1		
7	A	Blue	1-967650-1	*	1-1718230-1	_	
1	В	Gray	2-967650-1	*	2-1718230-1	_	_
	C	Green	3-967650-1	*	3-1718230-1	-	

^{*)} Suitable Covers/Adapters see Accessories.

Technical Features

No. of Positions:

5-7 Positions

Housing Material:

PBT GF 20

Wire Size Range:

2.5 mm² Max.

Product Specification:


108-18622

Application Specification:

114-18255-0

Product Group Drawing:

1355392



Pin Housings

No. of Keying Options Color Pin Cover Mating Socket Housing Socket Housing Nation Right-Angle 1718230-3 * 967650-3 -	
5 A Black 1718230-3 * 967650-3 -	g PCB Header e Vertical
	_
6 A Black 1718230-2 * 967650-2 -	_
Black 1718230-1 * 967650-1	
Blue 1-1718230-1 * 1-967650-1	
B Gray 2-1718230-1 * 2-967650-1	_
C Green 3-1718230-1 * 3-967650-1	

^{*)} Suitable Covers/Adapters see Accessories.


Accessories

Accessories




Description	Color	Part No.
Mounting ring for pin housing	Black	965687-1
Front cover for 2-4 pos. socket housing 967325	Black	185636-1
Erent cover for 2 / A pee, and 5 / pee, nin housing 067/02 and 1719/20	Black	1394277-1
Front cover for 2-4 pos. and 5-7 pos. pin housing 967402 and 1718230	DIACK	1394277-2
Right-angle adapter with universal clamp	Black	965576-1
Vertical adapter with universal clamp	Black	965784-1
Right-angle adapter for NW 7.5 mm diameter corrugated tubing	Black	185793-1
Right-angle adapter for NW 8.5 mm diameter corrugated tubing	Black	965577-1
Right-angle adapter for NW 10 mm diameter corrugated tubing	Black	965783-1
Vertical adapter for NW 7.5 mm diameter corrugated tubing	Black	185792-1
Vertical adapter for NW 8.5 mm diameter corrugated tubing	Black	965785-1
Vertical adapter for NW 10 mm diameter corrugated tubing	Black	965786-1
Right-angle adapter 4/7 position for hose	Black	1534789-1
Vertical adapter 4/7 position for hose	Black	1534791-1
Vertical adapter 4/7 position for jacketed cable 5.2-6.5 mm	Black	1418916-1
Vertical adapter 4/7 position for jacketed cable 6.0-9.5 mm	Black	1418917-1
Right-angle adapter 4/7 position for jacketed cable 5.2-6.5 mm	Black	1418918-1
Right-angle adapter 4/7 position for jacketed cable 6.0-9.5 mm	Black	1418919-1

Sealed Socket Connector Assembly



Sealed Pin Connector Assembly



Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Sealed Diameter 1.5 mm/Diameter 2.5 mm Pin and Socket Housings

Technical Features

No. of Positions:

31 Positions

Housing Material:


PBT GF 20

Wire Size Range:

- up to 2.5 mm² FLR Max. (diameter 1.5 mm)
- up to 4.0 mm² FLR Max. (diameter 2.5 mm)

Product Specification: 108-18742

Application Specification: 114-18449



Sealed Mixed Socket Housing

No. of	Hausina		ı	Part Numbers			
No. of Positions	Housing Color	Socket Housing					
31	Black	1394081-1	1394089-1 (Vertical)	-	-	-	
31	DIACK	_	1394816-1 (45° Angle)	-	-	-	

^{*} For adaption to corrugated tubes NW 22.

Technical Features

No. of Positions: 31 Positions

Housing Material: PBT GF 20


Wire Size Range:

- up to 2.5 mm² FLR Max. (diameter 1.5 mm)
- up to 4.0 mm² FLR Max. (diameter 2.5 mm)

Product Specification: 108-18742

Application Specification:

114-18449




Sealed Mixed Pin Housing

No. of	Uavaina			Part Numbers		
No. of Positions	Housing Color	Pin	Adapter	Mating	Mating PC	
		Housing	Cap*	Socket Housing	Right-Angle	Vertical
31	Black	1718232-1	1394089-1 (Vertical)	-	-	-
	DIdCK	-	1394816-1 (45° Angle)	-	-	-


^{*} For adaption to corrugated tubes NW 22.

Sealed Diameter 1.5 mm/Diameter 2.5 mm Pin and Socket Housings

Cap for 31 Positions
Pin and Socket Housing
for Corrugated Tubes
nominal Width 22.0 mm



Cap 45° for 31 Positions Pin and Socket Housing for Corrugated Tubes nominal Width 22.0 mm



Connectors for Diesel Fuel Injector

Technical Features

No. of Positions: 2 Positions

Housing Material:

Nylon 6.6 GF

Wire Size Range:


0.2-2.5 mm²

Product Specification:

108-3428-1

Application Specification:

114-3219



Socket Housing

No. of	V avrimer	Haveine	Socket Housing Cover Mating Pin Housing 1337245-3				
No. of Positions	Keying Options	Housing Color		Cover		Mating PCI Right-Angle	3 Header Vertical
2	-	Black	1337245-3	-	-	-	-

Technical Features

No. of Positions:

4 Positions

Housing Material:

Nylon 6.6 GF

Wire Size Range:


 $0.2 - 2.5 \text{ mm}^2$

Product Specification:

108-3442

Application Specification:

114-3219



Socket Housing

No. of	No. of Keying Positions Options	Harrian.	Part Numbers				
Positions		Housing Color	Socket Housing	Cover	Mating Pin Housing	Mating PCI Right-Angle	B Header Vertical
4	-	Black	1337352-1	-	-	-	-

For Special Socket Contacts see Page 26-5.

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Socket Contacts for Diesel Fuel Injector Connector

Technical Features

Wire Size Range: 0.5-2.5 mm²

Insulation Diameter:

1.2-3.0 mm

Contact Material:

CuNi18Zn20

Contact Finish:

Blank

Current Carrying Capacity:


12 A max.

Product Specification:

108-18028

Application Specification:

114-18040



Socket Contacts for Diesel Fuel Injector Connector

Wire Size	Wire Size Range Insulation Diameter (mm) (mm²) FLK FLR		Material			Part Nu	mbers		
			and Finish	Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator*	Hand Tool
0.5–1.0	-	1.2–2.1	CuNi18Zn20, blank	1-929989-0	4,000	1-962998-0	500	2-878485-2	734289-1
1.0–2.5	-	2.2–3.0	CuNi18Zn20, blank	1-929990-0	3,800	1-962999-0	500	2-878486-2	734289-2

^{*} This Applicator Part Number is only one of a part number selection.

Please call your local Tyco Electronics representative for personal assistance or visit our website.

Sealed Socket Housing with Secondary Locking Device

Technical Features


No. of Positions: 66 Positions


Housing Material: PBT GF 20

Wire Size Range: 4.0 mm² FLR Max.

Product Specification: 108-18734

Application Specification: 114-18424





Sealed Socket Housings with Secondary Locking Device

No. of Positions	Varian	Univalen			Part Numbers		
	Keying Options	Housing Color	Socket Housing	Cover	Mating Pin Housing	Mating PCI Right-Angle	3 Header Vertical
	^	Natural	1-1394748-1	1718010-1	1-1394750-1		
	А	Naturai	1-1394748-2	1718010-1	1-1394750-1	-	
66	В	Gray	2-1394748-1	1718010-1	2-1394750-1	-	
66	С	Blue	3-1394748-1	1718010-1	3-1394750-1		_
	D	Green	4-1394748-1	1718010-1	4-1394750-1	-	
	Spare Part F	Black	8-1394748-2	1718010-1	8-1394750-1	-	

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 - Issued 3-2010

Sealed Pin Housing with Secondary Locking Device

Technical Features


No. of Positions: 66 Positions

Housing Material: PBT GF 20

Wire Size Range: 4.0 mm² FLR Max.


Product Specification: 108-18734

Application Specification: 114-18424



Sealed Pin Housings with Secondary Locking Device


No. of Positions	Keying Options	Housing Color	Part Numbers				
			Pin Housing	Adapter	Mating Socket Housing	Mating PCI Right-Angle	3 Header Vertical
66 .	А	Natural	1-1394750-1	1534407-1	1-1394748-1 / -2		
	В	Gray	2-1394750-1	1534407-1	2-1394748-1		
	С	Blue	3-1394750-1	1534407-1	3-1394748-1	-	-
	D	Green	4-1394750-1	1534407-1	4-1394748-1		
	Spare Part F	Black	8-1394750-1	1534407-1	8-1394748-2		





Numerical Index

Part Number	Page	Part Number	Page	Part Number	Page
185636-1	26-17	929971-1	26-8	962977-7	26-8
185792-1	26-17	929971-7	26-8	962977-8	26-8
185793-1	26-17	929971-8	26-8	962978-1	26-8
539972-1	26-4	929972-1	26-8	962978-7	26-8
734285-1	26-5, 26-8 ,	929973-1	26-8	962978-8	26-8
	26-9	929974-1	26-8	962979-1	26-8
734285-2	26-5, 26-8 ,	929974-4	26-8	962980-1	26-8
	26-9	929974-7	26-8	962981-1	26-8
734285-3	26-8, 26-9 ,	929974-8	26-8	962981-4	26-8
734289-1	26-5, 26-6 ,	1-929974-4	26-8	962981-7	26-8
	26-8, 26-9 ,	929975-1	26-8	962981-8	26-8
	26-23	929975-4	26-8	1-962981-4	26-8
734289-2	26-5, 26-6 ,	929975-7	26-8	962982-1	26-8
	26-8, 26-9 ,	929975-8	26-8	962982-4	26-8
	26-23	929985-1	26-5	962982-7	26-8
828904-1	26-10	929986-1	26-5	962982-8	26-8
828904-2	26-10	929986-4	26-5	962994-1	26-5
828904-3	26-10	929987-1	26-5	962995-1	26-5
828905-1	26-10	929988-1	26-5	962995-4	26-5
828920-1	26-10	929988-2	26-5	962996-1	26-5
828921-1	26-10	929989-1	26-5	962997-1	26-5
828921-2	26-10	929989-4	26-5	962997-2	26-5
828922-1	26-10	929989-7	26-5	962998-1	26-5
828922-2	26-10	929989-8	26-5	962998-4	26-5
828986-1	26-10	1-929989-0	26-5, 26-23	962998-7	26-5
2-878485-2	26-23	929990-1	26-5	1-962998-0	26-5, 26-23
2-878486-2	26-23	929990-4	26-5	962999-1	26-5
929962-1	26-9	929990-7	26-5	962999-4	26-5
929963-1	26-9	1-929990-0	26-5, 26-23	962999-7	26-5
929963-8	26-9	962966-1	26-9	1-962999-0	26-5, 26-23
1-929963-0	26-9	962967-1	26-9	965576-1	26-17
929964-1	26-9	962967-8	26-9	965577-1	26-17
1-929964-0	26-9	1-962967-0	26-9	965687-1	26-17
929965-1	26-9	962968-1	26-9	965702-1	26-4
929966-1	26-9	1-962968-0	26-9	965783-1	26-17
929966-7	26-9	962969-1	26-9	965784-1	26-17
929967-1	26-9	962970-1	26-9	965785-1	26-17
929967-4	26-9	962970-7	26-9	965786-1	26-17
929967-7	26-9	962971-1	26-9	1-967325-1	26-12, 26-13
929967-8	26-9	962971-4	26-9	1-967325-2	26-12, 26-13
1-929967-0	26-9	962971-7	26-9	1-967325-3	26-12, 26-13
1-929967-4	26-9	962971-8	26-9	2-967325-1	26-12, 26-13
929968-1	26-9	1-962971-0	26-9	2-967325-2	26-12, 26-13
929968-4	26-9	1-962971-4	26-9	2-967325-3	26-12, 26-13
929968-7	26-9	962972-1	26-9	3-967325-1	26-12
929968-8	26-9	962972-4	26-9	3-967325-2	26-12
929969-1	26-8	962972-7	26-9	3-967325-3	26-12
929970-1	26-8	962972-8	26-9	4-967325-1	26-12
929970-7	26-8	962976-1	26-8	4-967325-2	26-12
929970-8	26-8	962977-1	26-8	4-967325-3	26-12





Numerical Index

Part Number		Page
1-967402-1	26-12,	26-13,
		26-14
1-967402-2	26-12,	26-13,
		26-14
1-967402-3	26-12,	26-13,
		26-14
2-967402-1	26-12,	
2-967402-2	,	
2-967402-3	26-12,	26-13,
		26-14
967650-1		26-16
967650-2		26-16
967650-3		26-16
967650-4		26-16
1-967650-1		26-16
2-967650-1		26-16
3-967650-1		26-16
1-968968-1	26-13,	26-14
1-968968-2		26-14
1-968968-3		26-14
2-968968-3		26-14
6-968968-1		26-13
6-968968-2		26-13
6-968968-3		26-13
1241598-1		26-15
1337245-3		26-22
1337352-1		26-22
1394081-1		26-20

Part Number	Page
1394089-1	26-20
1394277-1	26-17
1394277-2	26-17
1394324-1	26-15
1394324-2	26-15
1394324-3	26-15
1394324-4	26-15
1-1394748-1	26-24, 26-25
1-1394748-2	26-24, 26-25
2-1394748-1	26-24, 26-25
3-1394748-1	26-24, 26-25
4-1394748-1	26-24, 26-25
8-1394748-2	,
1-1394750-1	26-24, 26-25
2-1394750-1	26-24, 26-25
3-1394750-1	26-24, 26-25
4-1394750-1	26-24, 26-25
8-1394750-1	26-24, 26-25
1394816-1	26-20
1418916-1	26-17
1418917-1	26-17
1418918-1	26-17
1418919-1	26-17
1534789-1	26-17
1534791-1	26-17
1-1579007-8	26-7
3-1579007-2	26-7
3-1579007-7	26-4

Part Number	Page
3-1579007-8	26-4
4-1579007-7	26-7
5-1579007-0	26-4
1703012-1	26-6
1703012-4	26-6
1703013-1	26-6
1703013-2	26-6
1703013-4	26-6
1703013-8	26-6
1703014-1	26-6
1703014-4	26-6
1703016-1	26-6
1703016-4	26-6
1703017-1	26-6
1703017-2	26-6
1703017-4	26-6
1703018-1	26-6
1703018-4	26-6
1703780-1	26-13
1718010-1	26-24
1718230-1	26-16
1718230-2	26-16
1718230-3	26-16
1-1718230-1	26-16
2-1718230-1	26-16
3-1718230-1	26-16
1718232-1	26-20

Disclaimer

While Tyco Electronics and its affiliates referenced herein have made every reasonable effort to ensure the accuracy of the information contained in this catalog, Tyco Electronics cannot assure that this information is error free. For this reason, Tyco Electronics does not make any representation or offer any guarantee that such information is accurate, correct, reliable or current. Tyco Electronics reserves the right to make any adjustments to the information at any time. Tyco Electronics expressly disclaims any implied warranty regarding the information contained herein, including, but not limited to, the implied warranties of merchantability or fitness for a particular purpose. Tyco Electronics' only obligations are those stated in Tyco Electronics' Standard Terms and Conditions of Sale. Tyco Electronics will in no case be liable for any incidental, indirect or consequential damages arising from or in connection with, including, but not limited to, the sale, resale, use or misuse of its products. Users should rely on their own judgment to evaluate the suitability of a product for a certain purpose and test each product for its intended application.

In case of any potential ambiguities or questions, please don't hesitate to contact us for clarification.

www.tycoelectronics.com/automotive

AMP, TE (Logo) and Tyco Electronics are trademarks of the Tyco Electronics Group of Companies and its Licensors.

Connector System for Circular Contacts

Section Catalog 1654286-2 Revised 12-2009 Main Catalog 1654400-1 Chapter 26 – Issued 3-2010

Engineering Notes

