


Machine taps M DIN 371 HSS und HSSE-Co 5, ground



**Machine taps with reinforced shank
for through threads.**

Chamfer: type B, 4 - 5 threads with progressive tap
Thread: metric, DIN ISO 13
Flanks: relief-ground



Packing unit: individual plastic pack

Nominal thread size	Pitch mm	Thread core hole Ø ₁ mm	L ₁ mm	L ₂ mm	Ø ₂ mm
M 2	0,40	1,60	45,0	8,0	2,8
M 2,5	0,45	2,05	50,0	9,0	2,8
M 3	0,50	2,50	56,0	9,0	3,5
M 4	0,70	3,30	63,0	12,0	4,5
M 5	0,80	4,20	70,0	13,0	6,0
M 6	1,00	5,00	80,0	15,0	6,0
M 8	1,25	6,80	90,0	18,0	8,0
M 10	1,50	8,50	100,0	20,0	10,0

Nominal thread size	Article no. HSS	Article no. HSSE-Co 5	Article no. HSSE-Co 5 VAP	Article no. HSS-TiN	Article no. HSSE-Co 5 TiAlN
M 2	232 020	232 020 E	232 020 VA	232 020 T	232 020 EF
M 2,5	232 025	232 025 E	232 025 VA	232 025 T	232 025 EF
M 3	232 030	232 030 E	232 030 VA	232 030 T	232 030 EF
M 4	232 040	232 040 E	232 040 VA	232 040 T	232 040 EF
M 5	232 050	232 050 E	232 050 VA	232 050 T	232 050 EF
M 6	232 060	232 060 E	232 060 VA	232 060 T	232 060 EF
M 8	232 080	232 080 E	232 080 VA	232 080 T	232 080 EF
M 10	232 100	232 100 E	232 100 VA	232 100 T	232 100 EF

