

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0313721100](#)
Status: **Active**
Overview: Stac64 Single, Multi-Pocket and Hybrid Header System
Description: Stac64 Hybrid Receptacle Assembly, 10 Circuit, Gray, Polarization B

Documents:

3D Model	Application Specification AS-34729-020-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31300-931 (PDF)
Product Specification PS-31372-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-31372-100-001 (PDF)	

General

Product Family	Crimp Housings
Series	31372
Application	Power, Wire-to-Board
Comments	Polarization B, 6 x 1.50 and 4 x 2.8, Polarization B, 6 x 1.50 and 4 x 2.8
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	883906883416

Physical

Circuits (maximum)	10
Circuits Detail	10
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	8.060/g
Number of Rows	2
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 5.25mm
Polarized to Mating Part	Yes
Ports	10
Stackable	No
Temperature Range - Operating	-40° to +100°C

Electrical

Current - Maximum per Contact	22.0A, 30.0A
-------------------------------	--------------


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-31372-100-001, AS-34729-020-001
Packaging Specification	PK-31300-931
Product Specification	PS-31372-100-001
Sales Drawing	313729000-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[31372](#) Series

Mates With

[34696](#) Stac64 Right Angle Assembly. [34695](#)
Stac64 Vertical Assembly

Use With

MX150 Terminal [33012](#)