

## **N-channel SiC power MOSFET**

Datasheet


V <sub>DSS</sub>	1200V
R <sub>DS(on)</sub> (Typ.)	80mΩ
I <sub>D</sub> *1	31A
$P_D$	165W

# Outline TO-247-4L (1) (2)(3)(4)

#### Features

- 1) Low on-resistance
- 2) Fast switching speed
- 3) Fast reverse recovery
- 4) Easy to parallel
- 5) Simple to drive
- 6) Pb-free lead plating; RoHS compliant

#### ●Inner circuit



Please note Driver Source and Power Source are not exchangeable. Their exchange might lead to malfunction.

#### Application

- Solar inverters
- DC/DC converters
- Switch mode power supplies
- · Induction heating
- Motor drives

#### Packaging specifications

	Packing	Tube
	Reel size (mm)	-
Typo	Tape width (mm)	-
Type	Basic ordering unit (pcs)	30
	Taping code	C15
	Marking	SCT3080KR

### ◆Absolute maximum ratings (T<sub>vj</sub> = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit
Drain - Source Voltage		$V_{DSS}$	1200	V
Continuous Drain current	T <sub>c</sub> = 25°C	I <sub>D</sub> *1	31	А
Continuous Drain current	T <sub>c</sub> = 100°C	I <sub>D</sub> *1	22	А
Pulsed Drain current (T <sub>c</sub> = 25°C)		I <sub>D,pulse</sub> *2	77	А
Gate - Source voltage (DC)		$V_{GSS}$	-4 to +22	V
Gate - Source surge voltage (t <sub>surge</sub> < 300ns)		V <sub>GSS_surge</sub> *3	-4 to +26	V
Recommended drive voltage		V <sub>GS_op</sub> *4	0 / +18	V
Virtual Junction temperature		T <sub>vj</sub>	175	°C
Range of storage temperature		T <sub>stg</sub>	-55 to +175	°C

# ●Electrical characteristics (T<sub>vj</sub> = 25°C unless otherwise specified)

Darameter	Cymbol	Conditions		Values		
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
		$V_{GS} = 0V$ , $I_D = 1mA$				
Drain - Source breakdown voltage	V <sub>(BR)DSS</sub>	$T_{vj} = 25^{\circ}C$	1200	-	-	V
vollago		T <sub>vj</sub> = -55°C	1200	-	-	
		$V_{GS} = 0V, V_{DS} = 1200V$				
Zero Gate voltage Drain current	I <sub>DSS</sub>	$T_{vj} = 25^{\circ}C$	-	1	10	μΑ
Diam current		T <sub>vj</sub> = 150°C	-	2	-	
Gate - Source leakage current	I <sub>GSS+</sub>	$V_{GS} = +22V, \ V_{DS} = 0V$	-	-	100	nA
Gate - Source leakage current	I <sub>GSS-</sub>	$V_{GS} = -4V$ , $V_{DS} = 0V$	-	-	-100	nA
Gate threshold voltage	V <sub>GS (th)</sub>	$V_{DS} = 10V$ , $I_D = 5mA$	2.7	-	5.6	V
		$V_{GS} = 18V, I_D = 10A$				
Static Drain - Source on - state resistance	R <sub>DS(on)</sub> *5	$T_{vj} = 25^{\circ}C$	-	80	104	mΩ
on state resistance		T <sub>vj</sub> = 150°C	-	136	-	
Gate input resistance	$R_{G}$	f = 1MHz, open drain	-	12	-	Ω


#### ●Thermal resistance

Parameter	Symbol	Values			Unit
r al allielei		Min.	Тур.	Max.	Offic
Thermal resistance, junction - case	$R_{thJC}$	-	0.70	0.91	K/W

●Typical Transient Thermal Characteristics

Symbol	Value	Unit
R <sub>th1</sub>	8.52×10 <sup>-2</sup>	
R <sub>th2</sub>	4.15×10 <sup>-1</sup>	K/W
R <sub>th3</sub>	2.06×10 <sup>-1</sup>	

Symbol	Value	Unit
$C_{th1}$	1.22×10 <sup>-3</sup>	
$C_{th2}$	6.20×10 <sup>-3</sup>	Ws/K
C <sub>th3</sub>	3.49×10 <sup>-2</sup>	



# $\bullet \textbf{Electrical characteristics}$ (T $_{vj} = 25 \, \oplus \, C$ unless otherwise specified)


Doromotor	Symbol Conditions -	Values			Unit	
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Transconductance	<b>g</b> fs *5	$V_{DS} = 10V, I_{D} = 10A$	-	4.4	-	S
Input capacitance	C <sub>iss</sub>	V <sub>GS</sub> = 0V	-	785	-	
Output capacitance	C <sub>oss</sub>	V <sub>DS</sub> = 800V	-	75	ı	pF
Reverse transfer capacitance	$C_{rss}$	f = 1MHz	-	35	1	
Effective output capacitance, energy related	C <sub>o(er)</sub>	$V_{GS} = 0V$ $V_{DS} = 0V$ to 600V	ı	74	1	pF
Total Gate charge	Q <sub>g</sub> *5	$V_{DS} = 600V$ $I_{D} = 10A$	ı	60	ı	
Gate - Source charge	Q <sub>gs</sub> *5	$V_{GS} = 18V$	-	11	-	nC
Gate - Drain charge	Q <sub>gd</sub> *5	See Fig. 1-1.	-	31	-	
Turn - on delay time	t <sub>d(on)</sub> *5	$V_{DS} = 600V$	-	5	-	
Rise time	t <sub>r</sub> *5	$I_D = 15A$ $V_{GS} = 0V/+18V$	-	14	ı	20
Turn - off delay time	t <sub>d(off)</sub> *5	$R_G = 0\Omega, L = 750\mu H$ $L_G = 50nH, C_G = 10pF$	-	19	ı	ns
Fall time	t <sub>f</sub> *5	See Fig. 2-1, 2-2, 2-3.	-	13	-	
Turn - on switching loss	E <sub>on</sub> *5	E <sub>on</sub> includes diode reverse recovery.	-	168	-	1
Turn - off switching loss	E <sub>off</sub> *5		-	21	-	μJ

# ●Body diode electrical characteristics (Source-Drain) (T<sub>vj</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Conditions		Values	Unit	
raiailletei	Symbol	Coriditions	Min.	Тур.	Max.	Offic
Body diode continuous, forward current	I <sub>S</sub> *1	T <sub>c</sub> = 25°C	ı	1	31	А
Body diode direct current, pulsed	I <sub>SM</sub> *2	1 <sub>c</sub> – 25 0	ı	ı	77	А
Forward voltage	V <sub>SD</sub> *5	$V_{GS} = 0V, I_{S} = 10A$	ı	3.2	ı	V
Reverse recovery time	t <sub>rr</sub> *5	$I_F = 10A$ $V_R = 600V$	ı	17	ı	ns
Reverse recovery charge	Q <sub>rr</sub> *5	di/dt = 2500A/µs	ı	261	ı	nC
Peak reverse recovery current	: I <sub>rrm</sub> *5	$L_{\sigma} = 50$ nH, $C_{\sigma} = 10$ pF See Fig. 3-1, 3-2.	-	26	-	А

<sup>\*1</sup> Limited by maximum  $T_{vj}$  and for Max.  $R_{thJC}$ .

\*3 Example of acceptable  $V_{\text{GS}}$  waveform



Please note especially when using driver source that  $V_{\text{GSS\_surge}}$  must be in the range of absolute maximum rating.

\*5 Pulsed

TSQ50214-SCT3080KR

9.Nov.2022 - Rev.003

<sup>\*2</sup> PW  $\leq$  10µs, Duty cycle  $\leq$  1%

<sup>\*4</sup> Please be advised not to use SiC-MOSFETs with V<sub>GS</sub> below 13V as doing so may cause thermal runaway.

60

40

20

0

25

#### •Electrical characteristic curves

180 160 Power Dissipation: Pp [W] 140 120 100 80

Fig.1 Power Dissipation Derating Curve

Case Temperature : T<sub>C</sub> [°C]

125

175

Operation in this area is limited by R<sub>DS(on)</sub> Drain Current : I<sub>D</sub> [A] 10 PW = 10µs\* PW = 100µs PW = 1ms 1 PW = 10ms  $T_{c} = 25^{\circ}C$ Single Pulse \*Calculation(PW≤10µs) 0.1 0.1 10 100 1000 10000

Drain - Source Voltage : V<sub>DS</sub> [V]

Fig.2 Maximum Safe Operating Area

Fig.3 Typical Transient Thermal Impedance vs. Pulse Width

75




Fig.4 Typical Output Characteristics(I)




Fig.5 Typical Output Characteristics(II)






Fig.6  $T_{vj}$  = 25°C 3rd Quadrant Characteristics








Fig.9  $T_{vj} = 150^{\circ}$ C 3rd Quadrant Characteristics




Fig.10 Body Diode Forward Voltage vs. Gate - Source Voltage




Fig.11 Typical Transfer Characteristics (I)




Fig.12 Typical Transfer Characteristics (II)




Fig.13 Gate Threshold Voltage vs. Virtual Junction Temperature






Fig.14 Transconductance vs. Drain Current





Resistance vs. Virtual Junction Temperature 0.18  $V_{GS} = 18V$ Pulsed Static Drain - Source On-State 0.15 I<sub>D</sub>= 21A Resistance: R<sub>DS(on)</sub> [Ω]  $I_D=10A$ 0.12 -10A 0.09 0.06 0.03 0.00 0 -50 50 100 150 200 Virtual Junction Temperature : T<sub>vj</sub> [°C]

Fig.16 Static Drain - Source On - State

Fig.17 Static Drain - Source On - State Resistance vs. Drain Current 1 Static Drain - Source On-State Resistance :  $R_{DS(on)}\left[\Omega\right]$ 0.1  $T_{vj} = 150^{\circ}C$  $T_{vj}^{"} = 125^{\circ}C$  $T_{vi} = 75^{\circ}C$  $T_{vj} = 25^{\circ}C$  $V_{GS} = 18V$ Pulsed  $T_{vi} = -25^{\circ}C$ 0.01 10 100 1 Drain Current: ID [A]




Fig.19 Typical Capacitance vs. Drain - Source Voltage 10000  $C_{\text{iss}}$ 1000 Capacitance: C [pF]  $C_{oss}$ 100  $\mathsf{C}_{\mathsf{rss}}$ 10  $T_{vj} = 25^{\circ}C$ f = 1MHz  $V_{GS} = 0V$ 1 1 10 100 0.1 1000 Drain - Source Voltage : V<sub>DS</sub> [V]

25

T<sub>vj</sub> = 25°C

T<sub>vj</sub> = 25°C

15

15


0

100 200 300 400 500 600 700 800

Drain - Source Voltage : V<sub>DS</sub> [V]

Fig.20 Coss Stored Energy

Fig.21 Dynamic Input Characteristics







Fig.22 Typical Switching Time vs. External Gate Resistance 100  $T_{vj} = 25^{\circ}C$  $V_{DD} = 600V$ 80 V<sub>GS</sub>= +18V/0V t<sub>d(off)</sub> Switching Time: t [ns]  $I_D = 15A$  $L = 750 \mu H$ 60 40 20  $t_{d(on)}$ 0 10 20 30 0 External Gate Resistance :  $R_G[\Omega]$ 

vs. Drain - Source Voltage 350  $T_{vj} = 25^{\circ}C$  $I_{D} = 15A$ 300 V<sub>GS</sub>= +18V/0V Switching Energy: E [µJ]  $R_G = 0\Omega$ 250  $L = 750 \mu H$ 200 150 100 50  $\mathsf{E}_{\mathsf{off}}$ 0 300 400 500 600 700 800 900 Drain - Source Voltage: V<sub>DS</sub> [V]

Fig.23 Typical Switching Loss

Fig.24 Typical Switching Loss vs. Drain Current 1200 25°C  $T_{vj} =$  $V_{DD} = 600V$ 1000  $V_{GS} = +18V/0V$ Switching Energy: E [µJ]  $R_G = 0\Omega$ 800  $L = 750 \mu H$ 600 400  $\mathsf{E}_{\mathsf{on}}$ 200  $\mathsf{E}_{\mathsf{off}}$ 0 5 10 15 20 25 0 30 Drain Current: ID [A]



#### Measurement circuits and waveforms

Fig.1-1 Gate Charge Measurement Circuit




Fig.2-1 Switching Characteristics Measurement Circuit




Fig.2-2 Waveforms for Switching Time




Fig.2-3 Waveforms for Switching Energy Loss




Fig.3-1 Reverse Recovery Time Measurement Circuit







Fig.3-2 Reverse Recovery Waveform




# ●Package Dimensions






Unit: mm



Unit: mm

# **●**Die Bonding Layout





- •Front view of the packaging.
- •Dimensions are design values.
- •If the heat sink is to be installed, it should be in contact with the die bonding point.

Unit: mm

#### Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.

  Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact us.

# ROHM Customer Support System

http://www.rohm.com/contact/

#### **General Precaution**

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001