

START eco Downlight 215mm Round & Square Surface

START eco Downlight 215 1250lm 830 Surface
0054104



Product features

- START eco Downlight is an integrated LED surface mounted downlight with built-in non dimmable driver; 15W; 1250Lm; 83Lm/W; 3000K.



PRODUCT OVERVIEW

Product name	START eco Downlight 215 1250lm 830 Surface
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling surface mounting
General application	Retail
ETIM Class	EC002892
Warranty	3 years
Fixture luminous flux (lm)	1250
Luminaire efficacy (lm/W)	83
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	110
Glare control	< 28
Photobiological Risk Group	RG0
Total power consumption (W)	15
Electrical protection	Class II
Dimmable	No
Dimming method	N/A
LED Flickering Rate	Medium (21% - 40%)
Housing colour	RAL 9003 - Signal white
IP rating	IP20
IK rating	IK02
Product EAN number	5410288541044

DATA TABLE

General data

Product name	START eco Downlight 215 1250lm 830 Surface
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling surface mounting

START eco Downlight 215mm Round & Square Surface

START eco Downlight 215 1250lm 830 Surface
0054104

General application	Retail
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	3 years

Optical data

Fixture luminous flux (lm)	1250
Luminaire efficacy (lm/W)	83
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	110
Distribution type	Symmetric
Glare control	< 28
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	15
Mains voltage (V)	220-240V
Lamp power factor	0.5
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	115.0
Electrical protection	Class II
Control gear required	No
Dimmable	No
Dimming method	N/A
Drive current (mA)	135
Inrush Current (A)	12
Inrush Duration (µs)	200
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Medium (21% - 40%)
Max. Luminaires per 10A C Breaker	56
Max. Luminaires per 13A C Breaker	73
Max. Luminaires per 16A C Breaker	91
Max. Luminaires per 20A C Breaker	114
Max. Luminaires per 10A B Breaker	33
Max. Luminaires per 13A B Breaker	43
Max. Luminaires per 16A B Breaker	54
Max. Luminaires per 20A B Breaker	68

Lifetime data

Lifespan L70 B50	30000
------------------	-------

START eco Downlight 215mm Round & Square Surface

START eco Downlight 215 1250lm 830 Surface
0054104

Physical data

Housing colour	RAL 9003 - Signal white
IP rating	IP20
IK rating	IK02
Diffuser finish	Opal
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	215
Nominal Product Width (mm)	215
Nominal Product Height (mm)	34
Nominal Product Diameter (mm)	215
Weight (kg)	0.42


Packaging

Single packaging type	Carton
Product EAN number	5410288541044
Packaging single length / height (cm)	21.8
Packaging single width (cm)	4.8
Packaging single depth (cm)	22.0
DUN14 (outer)	15410288541041
Units per outer package	8
Packaging outer length / height (cm)	45.0
Packaging outer width (cm)	23.0
Packaging outer depth (cm)	22.0

Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

PHOTOMETRY



TECHNICAL DRAWINGS

START eco Downlight 215mm Round & Square Surface

START eco Downlight 215 1250lm 830 Surface
0054104

