

Torque wrench

DREMOMETER with calibration certificate according to DIN EN ISO 6789



Application:

The tightening value is set and read from the scale by means of rotary motion with angle key integrated in the handle end.

Execution:

- Audible and perceptible release when the tightening torque is reached
- Single key, one arm, with automatic release

Advantage:

- Special design ensures faultless operation
- The measured value or set torque is not changed
- Independent of handle position



Art. no.	52248 006
Brand	GEDORE
Manufacturer Part Number	1957694
Min. torque	2.5 Nm
Max. torque	12 Nm
Min./max. torque	2.5-12 Nm
Scale value torque	0.5 Nm
Tip size	1/4 inch
Error limit (%)	3 %
Length	211 mm
Calibration certificate	Yes
ISO	6789
Gross Weight	0.668 kg
Product Group	556

EAN

4002805929063